



Wire Protection & Management > Interconnect Devices > SolderSleeve Shield Terminators



SolderSleeve Shield Terminator Product Type: **Shield Terminator**

SolderSleeve Shield Terminator Operating Temperature (Max): **200 °C**

SolderSleeve Shield Terminator Expanded Inside Diameter (Min): **2.67 mm [.105 in]**

SolderSleeve Shield Terminator Recovered Inside Diameter (Max): **.76 mm [.03 in]**

Pre-Installed Lead: **No**

Features

Product Type Features

Splice Type	Shield Terminator
Temperature Indicator	Yes
Temperature Indicator Type	Fusible Ring
SolderSleeve Shield Terminator Product Type	Shield Terminator

Configuration Features

Pre-Installed Lead	No
--------------------	----

Termination Features

Termination Method	Solder
--------------------	--------

Dimensions

Overall Length	16.5 mm[.65 in]
Dielectric Outside Diameter (Max)	2.67 mm[200 in]
Shield Outside Diameter (Min)	1.4 mm[.055 in]
Jacket Outside Diameter	2.67 mm[.105 in]
SolderSleeve Shield Terminator Expanded Inside Diameter (Min)	2.67 mm[.105 in]
SolderSleeve Shield Terminator Recovered Inside Diameter (Max)	.76 mm[.03 in]

Usage Conditions

SolderSleeve Shield Terminator Operating Temperature (Max)	200 °C
Resistance Properties	Immersion Protection



Wire Temperature (Max)	150 °C
------------------------	--------

Industry Standards

Government Qualified	No
----------------------	----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # CJ2087-000
[HL2010E-KIT-120V](#)

Customers Also Bought



TE Part #5061850001
TMS-SCE MILITARY GRADE SLEEVES




TE Part #153282-000
342A012-25/225-0



TE Part #52197
TERMINAL,SOLIS R 6 10



TE Part #152882
18-16 PIDG RT NO 8 STUD ORANGE



TE Part #440727-000
B-040-20-N



TE Part #620004-000
D-103-00



TE Part #621056-000
D-142-52



TE Part #620005-000
D-104-00



TE Part #ZPF00000000020155
FMJ 11E 20-08 G

TE Part #3963810001
TMS-SCE-1/4-2.0-6

Documents

Product Drawings
S200-2-00

English

Datasheets & Catalog Pages
Raychem S200 Shield Terminators

English