




TE Internal #: NB11644001

Heat Shrink Tubing, Black, Dual Wall Type, 6 Expanded Inside Diameter (Min) .236 Expanded Inside Diameter (Min)

[View on TE.com >](#)

Heat Shrink Tubing



Primary Product Color: **Black**

Wall Type: **Dual**

Expanded Inside Diameter (Min): **6 mm [.236 in]**

Recovered Inside Diameter (Max): **2 mm [.079 in]**

Shrink Ratio: **3:1**

Features

Product Type Features

Product Family	ATUM
Wall Type	Dual

Electrical Characteristics

Voltage (Max)	.6 kV
---------------	-------

Body Features

Fluid Type	Aviation Fuel, Chemicals/Solvents, De-Icing Fluid, Diesel Fuel, Hydraulic Fluid, Lubricating Oil
Primary Product Color	Black
Shrink Ratio	3:1
Primary Product Material	Irradiated Modified Polyolefin
Flexibility	Semi-Flexible

Dimensions

Recovered Wall Thickness (Tolerance)	.3 mm[.012 in]
Recovered Wall Thickness (Nominal)	1 mm[.039 in]
Expanded Inside Diameter (Min)	6 mm[.236 in]



Recovered Inside Diameter (Max)	2 mm[.079 in]
Heat Shrink Tubing Size Range	2 – 6 mm[.079 – .236 in]

Usage Conditions

Fluid Resistance	Moisture, Splash Protection, Spray Protection
Shrink Temperature (Min)	80 °C
Heat Shrink Tubing Flammability	Flame-Retardant
Operating Temperature Range	-55 – 110 °C
Heat Shrink Tubing Resistance	Fluids, Mechanical Damage
Recovery Temperature	110 °C

Product Availability

Applicable Region	Global
-------------------	--------

Packaging Features

Packaging Method	Reel
------------------	------

Other

Meets Low Outgassing Requirements	No
Product Source	Czech Republic

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent

chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # CJ2087-000
HL2010E-KIT-120V



TE Part # EG1114-000
CV1981-ST-230V1600W-EU

Customers Also Bought



TE Part #1-163085-1
SPEC. PLATED




TE Part #100494-2
187 FASTON,REC.,16-20 AWG,TPBR



TE Part #1-968636-2
MQS, CONNECTOR HOUSING



TE Part #1-2236896-1
MCON, CONNECTOR HOUSING




TE Part #1379096-3
COV+LEV MQS 12W 90DEG BLK




TE Part #1-1452424-3
BLIND PLUG FOR MCON 1.2 CB (0,75 MM?)



TE Part #1-2141857-1
AMP MCP 2.8, CONTACT



TE Part #1333204-3
ANVIL, COMBINATION .080



TE Part #1333204-6
ANVIL, COMBINATION .080



TE Part #SP20310

Documents



Datasheets & Catalog Pages

[ATUM Pages from 9-1773447-9](#)

English

Product Specifications

[Product Specification](#)

English