

# VERSAFIT-1-0-SP. ✓ ACTIVE


TE Internal #: NB14284001

Heat Shrink Tubing, Black, Single Wall Type, 26.8 Expanded Inside Diameter (Min) 1.055 Expanded Inside Diameter (Min)

[View on TE.com >](#)



Heat Shrink Tubing



Primary Product Color: **Black**

Wall Type: **Single**

Expanded Inside Diameter (Min): **26.8 mm [ 1.055 in ]**

Recovered Inside Diameter (Max): **12.7 mm [ .5 in ]**

Shrink Ratio: **2:1**

## Features

### Product Type Features

Product Family	VERSAFIT
Wall Type	Single

### Electrical Characteristics

Voltage (Max)	.6 kV
---------------	-------

### Body Features

Fluid Type	Aviation Fuel, Chemicals/Solvents, De-Icing Fluid, Hydraulic Fluid, Lubricating Oil, Water
Primary Product Color	Black
Shrink Ratio	2:1
Primary Product Material	Irradiated Modified Polyolefin
Flexibility	Very Flexible

### Dimensions

Recovered Wall Thickness (Tolerance)	.25 mm[.01 in]
Recovered Wall Thickness (Nominal)	.88 mm[.035 in]
Expanded Inside Diameter (Min)	26.8 mm[1.055 in]



Recovered Inside Diameter (Max)	12.7 mm[.5 in]
Heat Shrink Tubing Size Range	12.7 – 26.8 mm[.5 – 1.055 in]

**Usage Conditions**

Fluid Resistance	Splash Protection
Shrink Temperature (Min)	70 °C
Heat Shrink Tubing Flammability	Highly Flame-Retardant
Operating Temperature Range	-55 – 135 °C
Heat Shrink Tubing Resistance	Fluids, Strain, Wrinkling
Recovery Temperature	90 °C

**Product Availability**

Applicable Region	Global
-------------------	--------

**Packaging Features**

Packaging Method	Reel
------------------	------

**Other**

Meets Low Outgassing Requirements	No
Product Source	Czech Republic

**Product Compliance**

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products

will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # CJ2087-000  
HL2010E-KIT-120V



TE Part # EG1114-000  
CV1981-ST-230V1600W-EU

## Customers Also Bought



TE Part #1658613-1  
IDC D-Sub: Plug Assembly, Low Profile, Signal, 2.77 mm



TE Part #1-745496-9  
IDC D-Sub: Plug Assembly, Wire to Wire, Signal, 2.77 mm



TE Part #1658621-9  
40 NOVO MIL/CTR 15DP, LEAD FREE



TE Part #1-770254-0  
UMNL II GROUND PIN LP DUPL BR



TE Part #1-6609103-7  
CORCOM P SERIES MULTI-FUNCTION INLET FIL




TE Part #1879642-1  
H8 100K 0.05% 15PPM




TE Part #160834-2  
PIDG PIGGY BACK FASTON TERMINAL



TE Part #1-644020-4  
Nylon Gold Plated Receptacle: 2.54 mm, With Mating Alignment, MTA 100



TE Part #108011-ZZ  
O RING



TE Part #R-8656  
RTD, STRR, P100, 385, .5%, .030T, H

## Documents

### Product Drawings

VERSAFIT-1-0-SP.

Heat Shrink Tubing, Black, Single Wall Type, 26.8 Expanded Inside Diameter (Min)  
1.055 Expanded Inside Diameter (Min)



## VERSAFIT-1-0-SP

English

---

### Datasheets & Catalog Pages

[VERSAFIT Pages from 9-1773447-9](#)

English

---

### Product Specifications

[Quality Specification](#)

English