




AMP

TE Internal #: 90800-2  
 Portable Crimp Tools, Commercial Crimp Tooling, Operator  
 Releasable & Adjustable, Removable/Interchangeable, TE Product  
 Specification (114-)

[View on TE.com >](#)

Application Tooling > Portable Crimp Tools



Tool Grade: **Commercial Crimp Tooling**  
 Ratchet Configuration: **Operator Releasable & Adjustable**  
 Die Sets Type: **Removable/Interchangeable**  
 Specification Type: **TE Product Specification (114-)**  
 TE Certification: **Upon Request for Fee**

**Features**

**Other**

Crimp Form-Wire Barrel Type	Open Barrel - F Crimp
Tool Grade	Commercial Crimp Tooling
Ratchet Configuration	Operator Releasable & Adjustable
Die Sets Type	Removable/Interchangeable
Specification Type	TE Product Specification (114-)
TE Certification	Upon Request for Fee
Power Technology Type	Battery, Electric, Manual
Tooling Type	Standard Die Envelope (SDE) Die Set

**Product Compliance**

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUL 2017 (174) SVHC > Threshold: Not Yet Reviewed



Halogen Content

Not Yet Reviewed for halogen content

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles'(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

## Compatible Parts



TE Part # CAT-038-DCCPB22  
D-Sub Connector Contacts: Pin, Brass, Signal, Size 22



TE Part # CAT-038-DCCSC22  
D-Sub Conn Contacts: Socket, Phosphor Bronze, Signal, Size 22



TE Part # 2280380-1  
KIT, BT, MICRO SDE, 110V




TE Part # 2280380-2  
KIT, BT, MICRO SDE, 220V




TE Part # 1658686-5  
SOCKET CONTACT,22 DF,STRIP,22-




TE Part # 1658686-6  
SOCKET CONTACT,22 DF,LP,22-28




TE Part # 216581-1  
HD-22 STIFTKONTAKT




TE Part # 216581-2  
HD-22 STIFTKONTAKT



TE Part # 216581-3  
HD-22 STIFTKONTAKT



TE Part # 748333-1  
HD22 CONT CS PIN,UNPLTD



TE Part # 748610-1  
CONT, HD22 CS SCKT, UNPL

## Customers Also Bought



TE Part #1658682-1  
D-Sub Crimp Recept Signal 26 Posn,  
Socket Size 22, Shell Size 2



TE Part #1658673-1  
D-Sub Crimp: Plug, Signal, 62 Posn,  
Pin Size 22, Shell Size 4



TE Part #1658670-4  
D-Sub Connector Contacts: Pin, Brass,  
Signal, Size 22



TE Part #1658686-4  
D-Sub Conn Contacts: Socket,  
Phosphor Bronze, Signal, Size 22



TE Part #1-1879075-4  
Power Resistor: Aluminum Housed, 75  
Watt



TE Part #1-1879353-0  
RR02 5% 10K AMMO



TE Part #YDTS26F21-16PNV001  
Straight Plug: D38999, 21-16 Insert,  
Electroless Nickel Plating



TE Part #1375963-2  
PC104 CONN NONSTKTHRU NO  
STNDO

## Documents

### Datasheets & Catalog Pages

[1-1773865-2\\_1015\\_Commercial Manual Hand Tools](#)

English

[Crimp Term Whitepaper-Use the Right Tool 1-1773953-1](#)

English

### Bottoming Dies

English

[CRIMPING WHERE FORM MEETS FUNCTION](#)

English

### Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English