



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)


EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Cadmium oxide (4.37% in Component Part) Cd (10% in Component Part) Article Safe Usage Statements: Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts






TE Part # 1393143-7
27E123=SOCKET,KRP,11,SCW,PLE




TE Part # 2-1419106-4
27E892=SOCKET,KRPA,11,OCTAL,PO

Also in the Series | Potter & Brumfield KRPA



Power Relays(60)




Relay Accessories, Sockets & Clips(5)

Customers Also Bought




TE Part #1473005-1
DDR2 SO DIMM Sockets



TE Part #104479-9
SHORT POINT CONT 15 DPLX STMPD LF



TE Part #2-1393763-3
V23100V4305C11




TE Part #1-2199299-5
DIP Socket: Standard, Stamped & Formed, Open, Tin



TE Part #1-1734827-3
AMP HPI 2.0MM HEADERS



TE Part #HD34-18-20PN-059
DEUTSCH HD30 HOUSINGS



TE Part #1-380991-0
10P CMNL HDR ASSY NATL



TE Part #104257-2
03 MTE RCPT HSG SR LATCH .100



TE Part #1437471-2
SSC12APA=120V 60HZ .1 TO 10 SE



TE Part #2-1423165-7
7024ABT=RLY,STD,OFF,4P,120V,5SEC, T OPT



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_9-1393101-8_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_9-1393101-8_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_9-1393101-8_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

KRPA, KRP, KA, KR 5 to 10 Amp General Purpose Relay

English

Industrial Relays Quick Reference Guide

English

Industrial Relays Quick Reference Guide

Japanese

Industrial Relays Quick Reference Guide

Product Specifications

Definitions, Handling, Processing, Testing and Use of Relays

English