



Identification & Labeling > Pre-Printed Markers > STD SNAP-ON MARKERS



Marker Style: **Snap-On**

Marker Size: **STD 01**

Compatible Cable Diameter Range: **1 – 1.4 mm [.04 – .055 in]**

Primary Product Color: **Yellow**

Marker Cut: **Straight**

[All STD SNAP-ON MARKERS \(881\)](#)

Features

Body Features

|                          |                  |
|--------------------------|------------------|
| Marker Style             | Snap-On          |
| Marker Size              | STD 01           |
| Primary Product Color    | Yellow           |
| Primary Product Material | Polyoxymethylene |

Dimensions

|                                 |                            |
|---------------------------------|----------------------------|
| Compatible Cable Diameter Range | 1 – 1.4 mm [.04 – .055 in] |
|---------------------------------|----------------------------|

Printer/Label Features

|                 |          |
|-----------------|----------|
| Marker Cut      | Straight |
| Printed Marking | E        |

Packaging Features

|                    |       |
|--------------------|-------|
| Packaging Method   | Strip |
| Packaging Quantity | 300   |

Other

|                       |       |
|-----------------------|-------|
| Printed Marking Color | Black |
|-----------------------|-------|

Product Compliance



For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                               |
|-----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                     |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                     |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                       |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2021 (211)<br>Candidate List Declared Against: JAN 2021 (211)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                           |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                  |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-T3437-ST2999  
STD SNAP-ON MARKERS

Also in the Series | Agastat 7000



Pre-Printed Markers(888)



Time Delay Relays(214)

Customers Also Bought



TE Part #1623788-8  
Wirewound Resistor: Vertical Mount



TE Part #2-2176404-5  
3550 130K 1%



TE Part #4-1768016-7  
BKM SELF LAMINATING VINYL LABELS



TE Part #2-215570-4  
PADDLE BOARD CONNECTOR



TE Part #967702-1  
AMP MCP, SFC, RECEPTACLE



TE Part #160811-8  
FF 250 REC 4-6MM2 PB



TE Part #2836038-2  
OCEAN\_2.0\_APPLICATOR-S-209F272F



TE Part #2836039-2  
OC-AT-S-FA-252F303OV-040-0836



TE Part #2837323-2  
OCEAN\_2.0\_Appliator-S-069F125OA

Documents

Product Drawings

STD01Y-E

English

Datasheets & Catalog Pages

STD and STB Technical Datasheet

English

IDENTIFICATION SELECTION GUIDE

English



Product Specifications

RW-2538 STD and STB work instruction

English