




Identification & Labeling > Labels > Standard Labels



Label Type: **Blank Labels**

Label Style: **Die-Cut**

Label Adhesive Type: **Permanent**

UL Listed: **No**

Label Width: **20 mm [.787 in]**

Features

Product Type Features

Label Type	Blank Labels
------------	--------------

Body Features

Label Color	Yellow
-------------	--------

Usage Conditions

Operating Temperature Range	0 – 70 °C[32 – 158 °F]
-----------------------------	------------------------

Printer/Label Features

Recommended Printer	See TE Document 411-121005 the Printer Product Ribbon Matrix
Recommended Printer Ribbon	See Printer Ribbon Matrix
Printer Technology	Thermal Transfer
Label Style	Die-Cut
Label Width	20 mm[.787 in]
Label Height	8 mm[.314 in]
Label Material	Polyamide

Industry Standards

UL Listed	No
-----------	----

Packaging Features

Packaging Quantity	10000
Packaging Method	Package



Other

Label Adhesive Type	Permanent
---------------------	-----------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2019 (197) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts













TE Part # 4-1768017-4

EET-0615G-4

Customers Also Bought



 <p>TE Part #154665-000 Bulbous Heat Shrink Boots: Lipped, Straight</p>	 <p>TE Part #1-968879-1 TIMER, CONNECTOR HOUSING</p>	 <p>TE Part #1670365-1 HEAVY DUTY SEALED CONNECTOR BACKSHELLS</p>	 <p>TE Part #174354-2 ECONOSEAL, CONNECTOR HOUSING</p>
 <p>TE Part #F16068-000 HX-SCE LOW FIRE HAZARD SLEEVES</p>	 <p>TE Part #171661-1 Econoseal Receptacles and Tabs</p>	 <p>TE Part #1-936124-2 MQS, CONNECTOR HOUSING</p>	 <p>TE Part #1863003-1 09P UMNL PLUG HSG</p>
 <p>TE Part #1742513003 FLHTC0311-1.00-0</p>	 <p>TE Part #1-965600-1 MQS KAPPE 8P</p>		

Documents

Product Drawings
EET-0820G-4

English

Datasheets & Catalog Pages
EET-G-4_THERMAL_TRANSFER_LABELS

English