TMS-SCE-1K-1-1/2-2.0-S1-9 ✔ ACTIVE


TMS-SCE

TE Internal #: 9328830001

TMS-SCE, Printable Tubing, Ladder Printable Tubing Type, Military Printable Tubing Grade, 3:1 Printable Tubing Shrink Ratio, White, 1 Prescore

View on TE.com >

Identification & Labeling > Printable Tubing > TMS-SCE MILITARY GRADE SLEEVES



Printable Tubing Type: **Ladder**

Printable Tubing Grade: **Military**

Printable Tubing Shrink Ratio: **3:1**

Primary Product Color: **White**

Number of Prescores: **1**

All TMS-SCE MILITARY GRADE SLEEVES (94)

Features

Product Type Features

Printable Tubing Type	Ladder
Printable Tubing Grade	Military

Body Features

Printable Tubing Shrink Ratio	3:1
Primary Product Color	White
Markers per Sleeve	2

Dimensions

Product Length	25 mm[1 in]
Supplied Inner Diameter	38.1 mm[1.5 in]
Recovered Inside Diameter	19 mm, 19.05 mm[.75 in]
Compatible Cable Diameter Range	20.9 – 33. mm[.825 – 1.3 in]

Usage Conditions

Operating Temperature Range	-55 – 135 °C[-67 – 275 °F]

Operation/Application

Recommended Ribbon	See TE Document 411-121005 the Printer Product Ribbon Matrix

Printer/Label Features

Recommended Printer	See TE Document 411-121005 the Printer Product Ribbon Matrix
Printer Technology	Thermal Transfer
Number of Prescores	1

Packaging Features

Packaging Quantity	1000

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 1-2186500-1
T3212-PRINTER



TE Part # 1-2186502-1
T3224-PRINTER



TE Part # 1-2186503-1
T3224-SWARE-PRINTER



TE Part # CP8122-000
T6112DS-PRINTER




TE Part # 1-2186501-1
T3212-SWARE-PRINTER

Also in the Series | TMS-SCE




Printable Tubing(142)


Customers Also Bought




TE Part #1958448-1
TERMINAL,PIDG, RT, IR, 16 AWG, #6 STUD



TE Part #100526-5
Z-PACK F.CODING KEY



TE Part #384306-002
44A1141-20-3/5/6/9-9



TE Part #1340650001
TMS-SCE MILITARY GRADE SLEEVES



TE Part #EC7553-000
HL LOW FIRE HAZARD MARKERS



TE Part #5058654004
RNF-3000 Single Wall Stick Heat Shrink



TE Part #1-292135-2
CT BOX HDR V ASSY 12P SHORT TIN



TE Part #8354103001
100G1161-0.4-A069CK0042



TE Part #3843063001
44A1141-20-3/5/6/9-9

Documents

Product Drawings

TMS-SCE-1K-1-1/2-2.0-S1-9

English

Datasheets & Catalog Pages

IDENTIFICATION SELECTION GUIDE

English

Instruction Sheets

Instruction Sheet (non U.S.)

English