




Relays, Contactors & Switches > Relays > Automotive Relays > Automotive Plug-In Relays > Relay Sockets



Relay Socket Type: **Printed Circuit Board**

Relay Socket For Use With: **Plug-In Mini ISO Relays**

Features

Product Type Features

|              |        |
|--------------|--------|
| Product Type | Socket |
|--------------|--------|

Contact Features

|                   |                       |
|-------------------|-----------------------|
| Relay Socket Type | Printed Circuit Board |
|-------------------|-----------------------|

Operation/Application

|                           |                         |
|---------------------------|-------------------------|
| Relay Socket For Use With | Plug-In Mini ISO Relays |
|---------------------------|-------------------------|

Other

|                        |                          |
|------------------------|--------------------------|
| Additional Information | Socket for PCB Soldering |
|------------------------|--------------------------|

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

|                                               |                                                                                                                               |
|-----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                     |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                     |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                       |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2021 (211)<br>Candidate List Declared Against: JAN 2021 (211)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                           |
| Solder Process Capability                     | Not reviewed for solder process capability                                                                                    |



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 60249-1  
FF 250 REC 16-12AWG BR

Also in the Series | Socket for Mini Relays



Relay Sockets(6)

Customers Also Bought



TE Part #1-640456-0  
Polyester Vertical PCB Header: 2.54 mm, Unshrouded, No Mating Alignment



TE Part #1-1879417-9  
CPF 0603 1M0 0.1% 25PPM 1K RL



TE Part #1-2176347-9  
CRGCQ 2010 330R 1%



TE Part #1-2176348-7  
CRGCQ 2010 470R 5%



TE Part #1-2176389-5  
RQ 1206 150R 0.1% 10PPM 5K RL

TE Part #1-2176312-3  
RP 1E 0.1W 16K5 0.1% 25PPM 1K RL

TE Part #T4140412051-000  
M12 Panel Mount PCB

TE Part #1393310-2  
VCFM-1000=FROM SEC

TE Part #1217861-1  
250 FASTON,PCB TAB,TCBR

TE Part #1-826470-1  
2X11P MOD II SHROUDED HEADER, RT ANG.

Documents

Product Drawings

VCF4-1000=FROM SEC

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_1393310-3\_B.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_1393310-3\_B.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_1393310-3\_B.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Automotive Relay Application Notes

English

Connectors for Mini ISO, Connectors Production Production North America, Accessories

English

Product Specifications

Definitions, Handling, Processing, Testing and Use of Relays

English





Product Environmental Compliance

Product Compliance

English

Product Compliance

English