




Application Tooling > Portable Crimp Tools



Tooling Type: **Adaptor Assembly**

Features

Other

Tooling Type	Adaptor Assembly
--------------	------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Out of Scope - excluded from Halogen requirements
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



## Compatible Parts

TE Part # 395241-000

[AT-1319-22](#)

## Customers Also Bought

TE Part #354940-1

[PRO-CRIMPER III FRAME W/O DIES](#)

TE Part #321021

[PIDG RING \(26-22\)](#)

TE Part #172130-1

[FF 250 REC HSG 2P NYLON NAT](#)

TE Part #170342-1

[250 FASTON,REC.,20-14 AWG,BR](#)

TE Part #1-794611-1

[MICRO MNL RPT CNT,LS PC,15AU,L](#)

TE Part #1056445-1

[2834 7316 02](#)

TE Part #DTS26W23-35PN-6149

[D38999: Straight Plug, 23-35 Insert](#)

TE Part #2031245-1

[CCII AMP-LEAF CONT 24-18 ASSY](#)

TE Part #126312N001

[S02-04-W1-24-9-100CS2870](#)

TE Part #230287-3

[FIELD SERVICE INSERTION TOOL](#)

## Documents

### Product Drawings

[AT-1319-14](#)

English

### Datasheets & Catalog Pages

[Raychem Application Tooling](#)

English



[Crimp Term Whitepaper-Use the Right Tool 1-1773953-1](#)

English

[CRIMPING WHERE FORM MEETS FUNCTION](#)

English

---

**Product Specifications**

[Termination Procedure for 748 Series SolderTacts Contacts for Twisted Pair Cable D-602-0126, D-602-0127](#)

English