




Relays, Contactors & Switches > Relays > Relay Accessories, Sockets & Clips



Relay Accessory, Socket & Clip Product Type: **Socket**
Relay Accessory, Socket & Clip Socket Type: **Printed Circuit Board**
Grounding Provision: **With**
Relay Accessory, Socket & Clip Body Material: **Nylon**
Relay Accessory, Socket & Clip For Use With: **KHA Relays**

Features

Product Type Features

Terminal Configuration	PC
Relay Accessory, Socket & Clip Product Type	Socket
Relay Accessory Type	Socket

Configuration Features

Grounding Provision	With
---------------------	------

Body Features

Relay Accessory, Socket & Clip Body Material	Nylon
--	-------

Contact Features

Terminal Length	5.54 mm[.218 in]
Contact Plating Material	Tin
Contact Base Material	Spring Brass
Relay Accessory, Socket & Clip Socket Type	Printed Circuit Board
Pole Configuration	4



Termination Features

Number of Pins	14
----------------	----

Mechanical Attachment

Relay Accessory, Socket & Clip Mounting Type	Printed Circuit Board
--	-----------------------

Operation/Application

Relay Accessory, Socket & Clip For Use With	KHA Relays
---	------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 240°C

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



 TE Part # 5-1393122-5 KHAU-17D12-12=KH	 TE Part # 2-1393122-0 KHAU-17A11-120=KH	 TE Part # 1419111-2 20C217=SPRING,HOLD-DOWN,KH,.03	 TE Part # 2-1393122-6 KHAU-17A11N-120=KH
 TE Part # 2-1393122-8 KHAU-17A12-120=KH	 TE Part # 3-1393122-9 KHAU-17A18-120=KH	 TE Part # 4-1393122-3 KHAU-17D11-12=KH	 TE Part # 4-1393122-4 KHAU-17D11-24=KH
 TE Part # 7-1393122-0 KHAU-17D16-12=KH	 TE Part # 7-1393122-1 KHAU-17D16-24=KH	 TE Part # 4-1393123-1 KHU-17D11-24=KH	 TE Part # 1-1393122-9 KHAU-17A11-12=KH
 TE Part # 2-1393122-2 KHAU-17A11-240=KH	 TE Part # 2-1393122-9 KHAU-17A12-24=KH	 TE Part # 3-1393122-0 KHAU-17A12-240=KH	 TE Part # 3-1393122-2 KHAU-17A12H-120=KH
 TE Part # 3-1393122-8 KHAU-17A16-24=KH	 TE Part # 4-1393122-0 KHAU-17A18-240=KH	 TE Part # 4-1393122-2 KHAU-17D11-110=KH	 TE Part # 4-1393122-5 KHAU-17D11-48=KH

Also in the Series | [Potter & Brumfield KHA](#)




Power Relays(80)




Relay Accessories, Sockets & Clips(7)


Customers Also Bought



TE Part #1546074-4
4 POS 5.08MM TERMINAL BLOCK TOP VIEW



TE Part #1419111-2
20C217=SPRING, HOLD-DOWN, KH, 03



TE Part #1419106-3
27E023=SOCKET, KH, 14, PC, PHEN, BL



TE Part #1-1473562-4
RITS CONN. PLUG ASSY 4P RED



TE Part #1-794073-0
08P MINI UML HDR W/O DH SN LF



TE Part #1-640445-6
16P MTA156 HDR ASSY FL/STR SN



TE Part #1376164-1
BATTERY HOLDER ML621 ASSY



TE Part #1-1393143-1
27E128=SOCKET, R10, 10, PC, PHEN



TE Part #LL01-1AB04
RELAY - ULTRASONIC LIQUID LEVEL SWITCH



TE Part #1-1393253-7
W68-X2Q110-10=M6/M7/M9/W6/W7

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1419106-2_31.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1419106-2_31.3d_igs.zip



English

Customer View Model

[ENG_CVM_CVM_1419106-2_31.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[KH Sockets & Accessories](#)

English

[Industrial Relays Quick Reference Guide](#)

English

[Industrial Relays Quick Reference Guide](#)

Japanese

[Industrial Relays Quick Reference Guide](#)

Product Specifications

[Definitions, Handling, Processing, Testing and Use of Relays](#)

English

Product Environmental Compliance

[TE Material Declaration](#)

English