



T2K

TE Internal #: A23615-000

T2K, Standard Labels, PCB Identification, Die-Cut Label Style, High Temperature Permanent Acrylic Adhesive, UL Listed Yes, Label Width 22.9 mm [.9 in]

[View on TE.com >](#)

Identification & Labeling > Labels > Standard Labels > T2K WHITE POLYIMIDE LABELS



Label Type: PCB Identification

Label Style: Die-Cut

Label Adhesive Type: High Temperature Permanent Acrylic Adhesive

UL Listed: Yes

Label Width: 22.9 mm [.9 in ]

[All T2K White Polyimide Labels \(15\)](#)

Features

Product Type Features

Label Type	PCB Identification
------------	--------------------

Body Features

Label Color	White
-------------	-------

Usage Conditions

Operating Temperature Range	-40 – 300 °C[-40 – 572 °F]
-----------------------------	----------------------------

Printer/Label Features

Number of Labels Across	3
Recommended Printer Ribbon	See Printer Ribbon Matrix
Label Style	Die-Cut
Label Width	22.9 mm[.9 in]
Label Height	6.4 mm[.25 in]
Label Material	Polyimide
Label Thickness	118 Micron

Industry Standards

UL Listed	Yes
-----------	-----



Packaging Features

Packaging Quantity	10000
Packaging Method	Roll

Other

Label Adhesive Type	High Temperature Permanent Acrylic Adhesive
---------------------	---

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not lead free process capable

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # 1-2186500-1  
T3212-PRINTER



TE Part # 1-2186502-1  
T3224-PRINTER



TE Part # 1-2186503-1  
T3224-SWARE-PRINTER



TE Part # 1-2186501-1  
T3212-SWARE-PRINTER


Also in the Series

T2K




Standard Labels(15)


Customers Also Bought




TE Part #1415074-1  
RT4S5LC4




TE Part #207467-1  
CABLE CLAMP KIT,SZ 1




TE Part #2118614-1  
ANTENNA, LTE, METASPAN, PCB, TAB MOUNT




TE Part #602818-000  
CSL SELF LAMINATING POLYESTER LABELS




TE Part #208494-3  
CMC SERIES 3




TE Part #2-530664-3  
CONN LOW PRO 15 POS 125SOL-EYE




TE Part #1-87813-4  
34 MODII HDR DRRA SHRD .100CL



TE Part #200875-8  
SERIES "M" JACKSCREW SOCKET AS



TE Part #CX4639-000  
302A821-4/180-0



TE Part #1SNA399903R0200  
BADL



Documents

Product Drawings

T2K-229064-10-9

English

Datasheets & Catalog Pages

T2K labels

English

IDENTIFICATION SELECTION GUIDE

English