



WP

TE Internal #: A71160-000
WP, Standard Labels, Industrial Label, Die-Cut Label Style,
Permanent Acrylic Adhesive, UL Listed Yes, Label Width 101.6 mm
[4 in]
[View on TE.com >](#)

Identification & Labeling > Labels > Standard Labels > WP WHITE POLYESTER LABELS



Label Type: **Industrial Label**
Label Style: **Die-Cut**
Label Adhesive Type: **Permanent Acrylic Adhesive**
UL Listed: **Yes**
Label Width: **101.6 mm [4 in]**

[All WP White Polyester Labels \(29\)](#)

Features

Product Type Features

Label Type	Industrial Label
------------	------------------

Body Features

Label Color	White
-------------	-------

Usage Conditions

Operating Temperature Range	-40 – 150 °C[-40 – 302 °F]
-----------------------------	----------------------------

Printer/Label Features

Number of Labels Across	1
Recommended Printer Ribbon	See Printer Ribbon Matrix
Label Style	Die-Cut
Label Width	101.6 mm[4 in]
Label Height	50.8 mm[2 in]
Label Material	Polyester
Label Thickness	72 Micron

Industry Standards

UL Listed	Yes
-----------	-----



Packaging Features

Packaging Quantity	2500
Packaging Method	Roll

Other

Label Adhesive Type	Permanent Acrylic Adhesive
---------------------	----------------------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # 1-2186500-1
T3212-PRINTER



TE Part # 1-2186502-1
T3224-PRINTER



TE Part # 1-2186503-1
T3224-SWARE-PRINTER



TE Part # 1-2186501-1
T3212-SWARE-PRINTER

Also in the Series | WP




Standard Labels(29)

Customers Also Bought



TE Part #1-1624117-3
BMB-L 0805 300R



TE Part #1-1546306-6
16P.374" DR BARRIER STRIP



TE Part #1622257-1
LR0204 1% 56R



TE Part #130094
PIDG RING TONGUE TERMINALS



TE Part #YDTS26G13-04PDV001
D38999: Straight Plug, 13-04 Insert



TE Part #1-480699-0
02P UMNL CAP HSG NATL



TE Part #1-480698-0
02P UMNL PLUG HSG NATL



TE Part #1-480701-0
03P UMNL CAP HSG NATL



TE Part #1-448138-5
CONTACT SZ 20 POSTED PIN



TE Part #1586379-1
06P UMNL PLUG HSG NATL



Documents

Product Drawings

WP-101508-2.5-9

English

Datasheets & Catalog Pages

WP White Polyester labels

English

IDENTIFICATION SELECTION GUIDE

English