



CM-SCE-TP

TE Internal #: A83925-000
CM-SCE-TP, Printable Tags, Military, Operating Temperature
Range -55 – 135 °C [-67 – 221 °F], White
[View on TE.com >](#)

Identification & Labeling > Printable Tags > CM-SCE-TP MILITARY GRADE MARKERS



Printable Tag Grade: **Military**
Operating Temperature Range: -55 – 135 °C [-67 – 221 °F]
Primary Product Color: **White**

[All CM-SCE-TP MILITARY GRADE MARKERS \(8\)](#)

Features

Product Type Features

Printable Tag Grade	Military
---------------------	----------

Body Features

Primary Product Color	White
-----------------------	-------

Mechanical Attachment

Number of Tie-Wrap Holes	6
--------------------------	---

Dimensions

Tag Height	12.7 mm[.6 in]
Tag Length	50.8 mm[1.8 in]

Usage Conditions

Operating Temperature Range	-55 – 135 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Recommended Ribbon	See TE Document 411-121005 the Printer Product Ribbon Matrix
--------------------	--

Printer/Label Features

Recommended Printer	See TE Document 411-121005 the Printer Product Ribbon Matrix
Printer Technology	Thermal Transfer

Packaging Features



Packaging Quantity	250
--------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 1-2186500-1
T3212-PRINTER



TE Part # 1-2186502-1
T3224-PRINTER



TE Part # 1-2186503-1
T3224-SWARE-PRINTER



TE Part # 4-160968-1
CABLE TY 134X2.6 NAT




TE Part # 2-160975-1 CABLE TY 200X4.8 NAT	TE Part # 4-160968-2 CABLE TY 134X2.6 BLACK	TE Part # 4-160971-2 CABLE TY 140X3.6 BLACK	TE Part # 4-160975-2 CABLE TY 200X4.8 BLA
TE Part # 2-100715-1 CABLE TY 150X3,6NAT	TE Part # 2-100716-1 CABLE TY 200X4,8NAT	TE Part # 2-160970-2 CABLE TY 200X2.6 BLA	TE Part # 2-160978-1 CABLE TY 360X4,8NAT
TE Part # 4-160970-2 CABLE TY 200X2.6 BLA	TE Part # 4-160975-1 CABLE TY 200X4.8 NAT	TE Part # 4-160974-1 CABLE TY 178X4,8NAT	TE Part # 2-160977-2 CABLE TY 290X4.8 BLA
TE Part # 2-160978-2 CABLE TY 360X4,8BLA	TE Part # 2-160968-1 FOAC CABLE TY NATURAL 134X2.6	TE Part # 1-2186501-1 T3212-SWARE-PRINTER	TE Part # 2-160968-2 CABLE TY 134X2.6 BLACK


Also in the Series | CM-SCE-TP

Printable Tags(9)


Customers Also Bought




TE Part #193495-000
D-150-0179



TE Part #208262-3
5009-328-0022



TE Part #104480-8
SHORT POINT RCP CONT LP




TE Part #159454-000
22759/35-22-9



TE Part #321892
DG 22-16COM 22-18MIL HT R 6



TE Part #036163-000
B-013-10



TE Part #ZPF000000000202709
DMC-MR 30-23 SN



TE Part #1577640-1
TERMINAL RT PIDG PEEK STRATO 14-12 AWG



TE Part #151440
PIDG 22 RING #8



TE Part #0561490001
RPS-18-12/2.0-9

Documents

Product Drawings
CM-SCE-TP-1/2-6H-9

English

Datasheets & Catalog Pages
CM-SCE-TP Technical datasheet

English

IDENTIFICATION SELECTION GUIDE

English

Product Specifications
CABLE MARKER INSTALLATION GUIDE

English

Cable Markers CM-SCE, CM-SCE-TP and HL

English