

3SBC1778A2

✓ ACTIVE

CII | CII 3SBC Relay


TE Internal #: 1617073-4

CII 3SBC Relay, 1/5-Size Relays, 1/5-Size Relay Contact
Arrangement 2 Form C, DPDT, 2 C/O, 18VDC 1/5-Size Relay Input
Voltage

[View on TE.com >](#)



Relays, Contactors & Switches > Relays > Mil-Aero Relays > 1/5-Size Relays



1/5-Size Relay Contact Arrangement: **2 Form C, DPDT, 2 C/O**

1/5-Size Relay Input Voltage: **18 VDC**

Coil Suppression Diode: **Without**

1/5-Size Relay Contact Current Rating: **2 A**

1/5-Size Relay Coil Voltage Rating: **18 VDC**

Features

Product Type Features

| | |
|----------------|-------------------------------------|
| Enclosure Type | Hermetically Sealed |
| Relay Type | Military/Aerospace High Performance |
| Coil Latching | Without |
| Product Type | Relay |
| MOSFET Driver | Without |

Configuration Features

| | |
|-------------------|---------|
| Transistor Driver | Without |
|-------------------|---------|

Electrical Characteristics

| | |
|------------------------------------|---------------------------|
| Actuating System | DC |
| Vibration | 30G's, 10 – 3000Hz |
| Coil Magnetic System | Non-Polarized, Monostable |
| Shock | 75G's, 6ms |
| Coil Power Measurement | Milliwatts |
| Coil Polarity Protection Diode | Without |
| 1/5-Size Relay Input Voltage | 18 VDC |
| Coil Suppression Diode | Without |
| 1/5-Size Relay Coil Voltage Rating | 18 VDC |



| | |
|---------------------------------------|--------------|
| 1/5-Size Relay Coil Resistance | 650 Ω |
| 1/5-Size Relay Coil Power Rating (DC) | 498 mW |

Contact Features

| | |
|---------------------------------------|-----------------------|
| 1/5-Size Relay Contact Arrangement | 2 Form C, DPDT, 2 C/O |
| 1/5-Size Relay Contact Current Rating | 2 A |

Termination Features

| | |
|------------------|-----------------------|
| Termination Type | Solder Hook Terminals |
|------------------|-----------------------|

Mechanical Attachment

| | |
|------------------------------|---------------|
| 1/5-Size Relay Mounting Type | Chassis Mount |
|------------------------------|---------------|

Usage Conditions

| | |
|-----------------------------|------------------------------|
| Operating Temperature Range | -65 – 125 $^{\circ}\text{C}$ |
|-----------------------------|------------------------------|

Product Compliance

For compliance documentation, visit the product page on TE.com>

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Not Compliant |
| EU ELV Directive 2000/53/EC | Not Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC |
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not lead free process capable |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling



based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts

TE Part # 1-1617076-1
3SBH1139A2 = M39016/14-002M

Also in the Series | CII 3SBC Relay

1/5-Size Relays(45)

Customers Also Bought

TE Part #YDTS26F25-29SAV001
D38999: Straight Plug, 25-29 Insert

TE Part #1056706-1
ADAPTER, SMA PLUG TO SMP PLUG

TE Part #1-1811927-4
8Q8 Size 25 Rcpt,A Key OD


TE Part #2-530745-1
MINI BX RCPT ASSY 110P SEALED

TE Part #5-120628-8
LOCKING TRIOMATE ASY 8P(L)LDFR

TE Part #530745-1
MINI-BOX RCPT ASSY 20P UNSEAL

TE Part #5767111-9
MICT,PLG,076,ASY,.025 TAPE CAP

TE Part #5787913-2
50SR CMP R/A LOP DOC PLUG ASSY



Documents

Product Drawings

3SBC1778A2 = M39016/13-112L

English

Datasheets & Catalog Pages

5-1773450-5_sec1_3SBC

English