

VERSAFLEX-03-0-SP

✓ ACTIVE

Raychem | Raychem VERSAFLEX


TE Internal #: C145614001

Raychem VERSAFLEX, Heat Shrink Tubing, Black, Braid Wall Type, Polyester, Non-Flame-Retardant, Box, Operating Temperature Range -50 – 150 °C

[View on TE.com >](#)



Heat Shrink Tubing



Primary Product Color: **Black**
Wall Type: **Braid**
Primary Product Material: **Polyester**
Heat Shrink Tubing Flammability: **Non-Flame-Retardant**
Packaging Method: **Box**

Features

Product Type Features

Product Family	VERSAFLEX
Wall Type	Braid

Body Features

Primary Product Color	Black
Primary Product Material	Polyester
Flexibility	Flexible

Dimensions

Heat Shrink Tubing Size Range	1 – 5 mm[.039 – .196 in]
-------------------------------	--------------------------

Usage Conditions

Fluid Resistance	Splash Protection
Heat Shrink Tubing Flammability	Non-Flame-Retardant
Operating Temperature Range	-50 – 150 °C
Heat Shrink Tubing Resistance	Mechanical Damage

Product Availability

Applicable Region	Global
-------------------	--------

Packaging Features

Packaging Method	Box
------------------	-----



Other

Meets Low Outgassing Requirements	No
Product Source	Europe

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # CJ2087-000
[HL2010E-KIT-120V](#)



TE Part # EG1114-000
[CV1981-ST-230V1600W-EU](#)



Also in the Series | Raychem VERSAFLEX



Heat Shrink Tubing(29)

Customers Also Bought



TE Part #170887-3
IS SHUR PLG 5 DIA NAT




TE Part #1-1747535-4
DYNAMIC 4000 REC AND TAB HSG



TE Part #1318143-1
TH/.025 CONNECTOR SYSTEM,
RECPT AND TAB



TE Part #1-1376430-8
HIGH PIN COUNT HEADER



TE Part #1-1623795-1
Wirewound Resistor: Horizontal Mount



TE Part #170889-2
SLEEVE DIA3 SHUR PLUG NAT



TE Part #1-1969599-8
18P PM PLUG VAL-U-LOK V2



TE Part #NB19334001
RNF-100-1/8-WH-SP



TE Part #172504-1
MIC CAP HSG 5P MK II



TE Part #170038-4
187 FASTON,REC.,20-16 AWG,TPPB

Documents

Datasheets & Catalog Pages

Application Tooling for Raychem Heat Shrink Product

English

VERSAFLEX - Expandable Braided Polyester Sleeving

English

Product Specifications



Quality Specification

English