




Wire Protection & Management > Heat Shrink Molded Shapes > Cable Entry Seals



Cable Entry Seal Seal Type: **Threaded**
Cable Entry Seal Material: **Nylon, Polyolefin**
Number of Branches/Legs: **4**
Cable Entry Seal Expanded Inside Diameter (Min): **10.2 mm [.4 in]**
Cable Entry Seal Recovered Inside Diameter (Max): **2.79 mm [.11 in]**

Features

Product Type Features

Thread Style	NPT
Angle	Straight
Product Type	Heat Shrink Cable Entry Seal

Configuration Features

Number of Branches/Legs	4
-------------------------	---

Body Features

Cable Entry Seal Seal Type	Threaded
Cable Entry Seal Material	Nylon, Polyolefin

Mechanical Attachment

Screw & Hole Thread Size	1/2-14
--------------------------	--------

Dimensions

Overall Length (Supplied)	57.15 mm[2.25 in]
Overall Length (Recovered)	57.15 mm[2.25 in]
Cable Entry Seal Expanded Inside Diameter (Min)	10.2 mm[.4 in]
Cable Entry Seal Recovered Inside Diameter (Max)	2.79 mm[.11 in]
Drill Size	.5
Cable Entry Seal Cable Diameter Range	3.05 – 8.64 mm[.12 – .34 in]

Usage Conditions



Cable Entry Seal Flammability	Flame-Retardant
-------------------------------	-----------------

Other

Comment	Molded part has hot-melt adhesive preinstalled.
---------	---

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CJ2087-000

[HL2010E-KIT-120V](#)

Also in the Series | Raychem CES



Cable Entry Seals(32)



Cable Transitions & Breakouts(5)




Feedthroughs(3)



Heat Shrink Boots(3)

Customers Also Bought




TE Part #1-2273105-4
M12 A-CODE FR/A LED SINGLE ENDED CABLE




TE Part #2273099-2
M12 A-CODE FEMALE R/A PIGTAIL



TE Part #3-2176369-8
RQ 0603 97R6 0.1% 10PPM 5K RL



TE Part #284046-6
TERMI-BLOK VERTICAL PLUG STACK



TE Part #284046-8
TERMI-BLOK VERTICAL PLUG STACK



TE Part #4-1609155-7
CORCOM P SERIES MEDIUM MULTI-FUNCTION IN




TE Part #293652-1
NECTOR S PCB CONN. ASSY. 90 DEG OUTLET



TE Part #293655-1
NECTOR S PCB PLUG STR HV-2 WHITE



TE Part #4-1734506-6
RCPT, 2.0MM, 46P,VRT MT, 8 Au", 2.6 ST



TE Part #F04061-000
CES-5-A250

Documents

Product Drawings

CES-2A-F1

English

CES-2A-F1

English

Datasheets & Catalog Pages

Raychem Molded Parts Visual Guide

English



Product Specifications

Raychem S1297 and /97 Hot Melt Adhesive

English

Product Specification

English