



Heat Shrink Tubing



Primary Product Color: **Red**

Wall Type: **Single**

Expanded Inside Diameter (Min): **10.2 mm [.4 in]**

Recovered Inside Diameter (Max): **3.81 mm [.15 in]**

Shrink Ratio: **3:1**

Features

Product Type Features

Product Family	SST
Wall Type	Single

Body Features

Fluid Type	De-Icing Fluid, Hydraulic Fluid, Lubricating Oil, Turbine Fuel
Primary Product Color	Red
Shrink Ratio	3:1
Primary Product Material	Irradiated Modified Polyolefin
Flexibility	Semi-Rigid

Dimensions

Recovered Wall Thickness (Tolerance)	1.78 mm[.07 in]
Cut Length	304.8 mm[12 in]
Expanded Inside Diameter (Min)	10.2 mm[.4 in]
Recovered Inside Diameter (Max)	3.81 mm[.15 in]
Heat Shrink Tubing Size Range	3.81 – 10.2 mm[.15 – .4 in]

Usage Conditions

Fluid Resistance	Moisture/Spray Protection
Shrink Temperature (Min)	90 °C



Heat Shrink Tubing Flammability	Non-Flame-Retardant
Operating Temperature Range	-55 – 110 °C
Heat Shrink Tubing Resistance	Abrasion, Fluids, Moisture
Recovery Temperature	121 °C

Product Availability

Applicable Region	Global
-------------------	--------

Packaging Features

Packaging Method	Box
------------------	-----

Other

Meets Low Outgassing Requirements	No
Product Source	US

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2326489-1
MODEL 105 TUNNEL OVEN, 36"
ENTRY, STAND A

TE Part # 955018-000
CLTEQ-M105-TUNNEL-OVEN

TE Part # CJ1047-000
VBH-1-BED-HTR-220V-3WR

Also in the Series | Raychem SST/SST-FR

Heat Shrink Tubing(65)

Customers Also Bought

TE Part #1-1579007-6
EXTRACTION TOOL

TE Part #42281-2
FF 250 REC 18-14AWG TPBR

TE Part #60888-1
058 PIN REC 26-22 .010PTPPHBZ

TE Part #2-1879355-8
RR03 5% 56K AMMO

TE Part #61070-2
FASTON .110 FLAG REC 22-18 AWG
BR

TE Part #1776313-4
TSB200004DS=EUROPA T-BL,14.5MM

TE Part #1-968946-1
TIMER, RECEPTACLE AND TAB

TE Part #HD36-24-18PN-059
DEUTSCH HD30 HOUSINGS

TE Part #5-147102-5
10 MODIV VRT DR 100/SFMNT 30AU

TE Part #1546011-3
3PCV-08-008=3PCV-ASSY



Documents

Datasheets & Catalog Pages

SST and SST-FR Pages from 9-1773447-9

English

Application Tooling for Raychem Heat Shrink Product

English

Measuring_Single_Wall_Tubing

English

Selecting_Correct_Tubing

English

Product Specifications

Quality Specification

English