



CII

TE Internal #: 1617149-4

TO-5/.100 Grid Relays, 2 Form C, DPDT, 2 C/O, 14VDC TO-5/.100

Grid Relay Input Voltage, Transistor Driver

View on TE.com >

Relays, Contactors & Switches > Relays > Mil-Aero Relays > TO-5/.100 Grid Relays



TO-5/.100 Grid Relay Contact Arrangement: 2 Form C, DPDT, 2 C/O

TO-5/.100 Grid Relay Input Voltage: 14 VDC

Coil Suppression Diode: Without

MOSFET Driver: Without

Transistor Driver: With

Features

Product Type Features

Enclosure Type	Hermetically Sealed
Relay Type	Military/Aerospace High Performance
Coil Latching	Without
Product Type	Relay
MOSFET Driver	Without

Configuration Features

Transistor Driver	With
-------------------	------

Electrical Characteristics

Coil Magnetic System	Non-Polarized, Monostable
Vibration	30G's, 10 – 3000Hz
Actuating System	DC
Shock	75G's, 6ms
Coil Power Measurement	Milliwatts
TO-5/.100 Grid Relay Input Voltage	14 VDC
Coil Suppression Diode	Without
Coil Voltage	26.5 VDC
TO-5/.100 Grid Relay Coil Resistance	3200 Ω
TO-5/.100 Grid Relay Coil Power Rating (DC)	219 mW



Coil Polarity Protection Diode	Without
TO-5/.100 Grid Relay Contact Switching Voltage (Max)	28

Contact Features

Contact Current Class	Low Level – 1 A
Pin Configuration	.175" Diameter Mounting Pad
TO-5/.100 Grid Relay Contact Arrangement	2 Form C, DPDT, 2 C/O
TO-5/.100 Grid Relay Contact Current Rating	1 A

Termination Features

Termination Type	PC Pins
------------------	---------

Mechanical Attachment

TO-5/.100 Grid Relay Mounting Type	Printed Circuit Board
------------------------------------	-----------------------

Usage Conditions

Operating Temperature Range	-65 – 125 °C
-----------------------------	--------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not lead free process capable

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for



substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts

TE Part # 2-1617031-0
HFW1201K45 = M39016/6-109L

Customers Also Bought

TE Part #815363-000
Heat Shrink Boots: Non Lipped, Straight

TE Part #340939-000
TXR21AB00-1612AI

TE Part #6-1617748-3
FCA-125-BX4

TE Part #170285-000
TXR18AB00B1204AI

TE Part #283142-000
44A0111-22-2L

TE Part #48861-1
HYP8/10 PLASTI-GRIP/10 2AWG DIE SET

TE Part #69463
HYP8/10 TERMINYL 4HDAWG DIE SET

TE Part #680112-000
D-150-22

TE Part #4-1617791-6
FCA-125-3605L=M83536/36-005L

TE Part #ZPF100000000007721
983-0SE 24-30 SN-L

Documents

CAD Files



3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1617149-4_O.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1617149-4_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1617149-4_O.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[5-1773450-5_sec1_MGS](#)

English