



Wire Protection & Management > Cable Braids



Cable Braid Product Type: **Braid**

Cable Braid Plating: **Nickel**

Braid Material: **Copper Alloy**

Braid Coverage: **90 %**

Features

Product Type Features

Cable Braid Product Type	Braid
--------------------------	-------

Electrical Characteristics

DC Resistance (Nominal)	28 mΩ
-------------------------	-------

Body Features

Cable Braid Plating	Nickel
Braid Material	Copper Alloy

Dimensions

Weight (Nominal)	8.5 kg/km
Cable Entry Diameter	3 – 4.5 mm[.118 – .177 in]
Length	32.08 ft

Usage Conditions

Operating Temperature Range	-65 – 200 °C
-----------------------------	--------------

Packaging Features

Packaging Method	Reel
Packaging Quantity	10

Other

Braid Coverage	90 %
----------------	------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>











Compatible Parts



TE Part # CJ2087-000  
HL2010E-KIT-120V

Customers Also Bought



 <p>TE Part #1-2308345-6 D-SUB BACKSHELL SIZE 4</p>	 <p>TE Part #1879215-7 CPF 0402 4K64 0.1% 25PPM 1K RL</p>	 <p>TE Part #1-1879215-7 CPF 0402 5K9 0.1% 25PPM 1K RL</p>	 <p>TE Part #2-1879215-9 CPF 0402 8K06 0.1% 25PPM 1K RL</p>
 <p>TE Part #1-2176412-1 5W XSM M/OX 5% 13R</p>	 <p>TE Part #2176215-9 CPF A 0402 1K43 0.1% 25PPM 1K RL</p>	 <p>TE Part #1-2176215-6 CPF A 0402 2K49 0.1% 25PPM 1K RL</p>	 <p>TE Part #1879507-8 CRGH0603 1% 158K 0.2W</p>
 <p>TE Part #1310963001 ACW0219-0.50-0(NS)</p>	 <p>TE Part #NB17902001 RW-175-3/4-X-STK</p>		

Documents

Product Drawings

LWB-103-3.0(10)

English

Datasheets & Catalog Pages

1654025\_Sec9\_Ray90\_Ray101\_Ray103

English

Harness Repair Products Quick Reference Guide

English