



Identification & Labeling > Labels > Standard Labels > HMM HIGH TACK METALIZED POLYESTER LABELS



Label Type: **Industrial Label**

Label Style: **Die-Cut**

Label Adhesive Type: **High Tack Acrylic Adhesive**

UL Listed: **Yes**

Label Width: **38.1 mm [1.5 in]**

All HMM HIGH TACK METALIZED POLYESTER LABELS (23)

Features

Product Type Features

Label Type	Industrial Label
------------	------------------

Body Features

Label Color	Matte Metalized Silver
-------------	------------------------

Usage Conditions

Operating Temperature Range	-40 – 150 °C[-40 – 302 °F]
-----------------------------	----------------------------

Printer/Label Features

Number of Labels Across	2
Recommended Printer Ribbon	See Printer Ribbon Matrix
Label Style	Die-Cut
Label Width	38.1 mm[1.5 in]
Label Height	19.1 mm[.75 in]
Label Material	Polyester
Label Thickness	107 Micron

Industry Standards

UL Listed	Yes
-----------	-----

Packaging Features



Packaging Quantity	5000
Packaging Method	Roll

Other

Label Adhesive Type	High Tack Acrylic Adhesive
---------------------	----------------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-2186500-1
T3212-PRINTER



TE Part # 1-2186502-1
T3224-PRINTER



TE Part # 1-2186503-1
T3224-SWARE-PRINTER



TE Part # 1-2186501-1
T3212-SWARE-PRINTER



Also in the Series | **HMM**

Standard Labels(23)

Customers Also Bought

TE Part #180351-2
FF 250 REC 4-6MM2 PTBR

TE Part #1-640722-0
09P UMNL STR/REL & INSRT NATL

TE Part #1-967325-1
CIRCULAR DIN HOUSINGS

TE Part #3-641123-4
Polyester Right Angle PCB Header:
2.54mm, Unshrouded, MTA 100

TE Part #3-641190-9
Nylon Gold Plated Receptacle: 2.54
mm, No Mating Alignment, MTA 100

TE Part #2-160984-2
FOAC CABLE TY BLACK 460X7.8

TE Part #3-640472-2
02P MTA156 ASSY ON TAPE LF

TE Part #F97088-000
WP WHITE POLYESTER LABELS

Documents

Product Drawings
HMM-381191-5-8A

English

Datasheets & Catalog Pages
HMM High Tack Matte Metalized Polyester

English

IDENTIFICATION SELECTION GUIDE
English