



Product Compliance


[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUL 2019 (201) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #1393788-3
AXICOM P2 STANDARD




TE Part #1-2199298-2
DIP Socket: Low Profile, Stamped & Formed, Open, Tin



TE Part #1735446-4
AMP HPI 2.0MM HEADERS




TE Part #1623127-1
CRG0805 1% 180R



TE Part #1-5353190-0
[.6FHR04H,140,S,GIG,08/Sn,TR,NSYes](#)



TE Part #103638-5
[06 MTE HDR SRST LATCH .100CL](#)



TE Part #1-5530843-0
[CONN SEC II 43 POS 100C/L](#)



TE Part #1-1614959-1
[CPF0805 1M5 0.1% 25PPM 1K RL](#)



TE Part #1623402-1
[CRG1206 1% 100K](#)



TE Part #8-1393101-1
[KRP-11AN-120=KA/KB/KC/KR](#)

Documents

Product Drawings

[MSS2250G04=DPDT SL SW VERT AU](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1825263-2_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1825263-2_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1825263-2_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Environmental Compliance

[TE Material Declaration](#)

English