

MV-127127-10-8A

✓ ACTIVE

TE Internal #: E21545-000

Standard Labels, Void & Tamper Evident Labels, Die-Cut Label

Style, Permanent Acrylic Adhesive, UL Listed Yes, Label Width 12.7 mm [.5 in]

[View on TE.com >](#)



Identification & Labeling > Labels > Standard Labels > MV TAMPER EVIDENT POLYESTER LABELS



Label Type: **Void & Tamper Evident Labels**

Label Style: **Die-Cut**

Label Adhesive Type: **Permanent Acrylic Adhesive**

UL Listed: **Yes**

Label Width: **12.7 mm [.5 in]**

[All MV TAMPER EVIDENT POLYESTER LABELS \(22\)](#)

Features

Product Type Features

|            |                              |
|------------|------------------------------|
| Label Type | Void & Tamper Evident Labels |
|------------|------------------------------|

Body Features

|             |                        |
|-------------|------------------------|
| Label Color | Matte Metalized Silver |
|-------------|------------------------|

Usage Conditions

|                             |                            |
|-----------------------------|----------------------------|
| Operating Temperature Range | -40 – 150 °C[-40 – 302 °F] |
|-----------------------------|----------------------------|

Printer/Label Features

|                            |                           |
|----------------------------|---------------------------|
| Number of Labels Across    | 5                         |
| Recommended Printer Ribbon | See Printer Ribbon Matrix |
| Label Style                | Die-Cut                   |
| Label Width                | 12.7 mm[.5 in]            |
| Label Height               | 12.7 mm[.5 in]            |
| Label Material             | Polyester                 |
| Label Thickness            | 86 Micron                 |

Industry Standards

|           |     |
|-----------|-----|
| UL Listed | Yes |
|-----------|-----|

Packaging Features



|                    |       |
|--------------------|-------|
| Packaging Quantity | 10000 |
| Packaging Method   | Roll  |

Other

|                     |                            |
|---------------------|----------------------------|
| Label Adhesive Type | Permanent Acrylic Adhesive |
|---------------------|----------------------------|

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                               |
|-----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                     |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                     |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                       |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2021 (211)<br>Candidate List Declared Against: JAN 2021 (211)<br>Does not contain REACH SVHC |
| Halogen Content                               | Not Yet Reviewed for halogen content                                                                                          |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                  |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 1-2186500-1  
T3212-PRINTER



TE Part # 1-2186502-1  
T3224-PRINTER



TE Part # 1-2186503-1  
T3224-SWARE-PRINTER



TE Part # 1-2186501-1  
T3212-SWARE-PRINTER

Customers Also Bought



TE Part #2-1825011-4  
ASF42RG04=4PDT AUTOSLIDE



TE Part #5745437-3  
D-Sub Plug Assembly: Standard, Right Angle, Shell Size 4, 2.74mm




TE Part #2-1437558-5  
MTA206PPC=(MSTA) SW TOG P/C TE



TE Part #5-749877-5  
IDC D-Sub: Receptacle Assembly, Panel Mount, Signal, 1.27 mm



TE Part #YDTS20F13-35HNV001  
D38999: Square Flange, 13-35 insert



TE Part #102541-4  
12 AMPMODU MT COVER DR .100CL



TE Part #5-104439-6  
2X7 MTE RCPT SR PLAIN .100CL



TE Part #102393-4  
12 AMPMODU MT ASSY DR .100CL



TE Part #1064303-1  
9950 1100 23,OSMT CABLE ASSY



TE Part #204532-1  
AMPLIMITE,ASY,RCPT,FB,90,5

Documents

Product Drawings  
MV-127127-10-8A

English

Datasheets & Catalog Pages  
MV Tamper Evident Metalized Polyester

English

IDENTIFICATION SELECTION GUIDE  
English