




Terminals & Splices > Crimp Wire Pins, Tabs & Ferrules



Terminal & Splice Type: **Ferrule**
Crimp Wire Pin, Tab & Ferrule Terminal Type: **Ferrule**
Crimp Wire Pin, Tab & Ferrule Wire Insulation Diameter (Max): **2.9 mm [.114 in]**
Accepts Wire Insulation Diameter Range: **2.9 mm [.114 in]**
Heavy Duty: **No**

Features

Product Type Features

Crimp Wire Pin, Tab & Ferrule Barrel Type	Closed Barrel
Crimp Wire Pin, Tab & Ferrule Wire/Cable Type	Regular Wire
Sealable	No
Insulated	Yes

Body Features

Double Wire	No
Crimp Wire Pin, Tab & Ferrule Plating Material	Tin

Contact Features

Terminal Length	8 mm[.312 in]
Terminal & Splice Type	Ferrule
Crimp Wire Pin, Tab & Ferrule Terminal Type	Ferrule
Crimp Wire Pin, Tab & Ferrule Terminal Orientation	Straight

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions



2-Wire Size	17 AWG
Strip Length	10 mm[.394 in]
Crimp Wire Pin, Tab & Ferrule Wire Insulation Diameter (Max)	2.9 mm[.114 in]
Accepts Wire Insulation Diameter Range	2.9 mm[.114 in]
Wire Size	2050 CMA
Barrel Inside Diameter	3 mm[.117 in]
Crimp Wire Pin, Tab & Ferrule Material Thickness	.15 mm[.005 in]
Crimp Wire Pin, Tab & Ferrule Overall Length	14 mm[.551 in]

Usage Conditions

Insulation Requirement	Partially Insulated
Operating Temperature Range	105 °C[221 °F]

Operation/Application

Heavy Duty	No
------------	----

Packaging Features

Packaging Quantity	1000
Crimp Wire Pin, Tab & Ferrule Packaging Method	Strip

Other

Barrel Color	Red
--------------	-----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 539660-1

ADERENDHUELSEN-HNDZ

Customers Also Bought



TE Part #2308171-2

ZQSFP+ CAGE& CONN 2X2, EMI SPRING, BTB



TE Part #1-2040586-1

DYNAMIC 4000 REC AND TAB CONT



TE Part #2-1735481-1

Free Height Receptacle Conn: Board-Board, Vertical, 40, 0.8mm



TE Part #2-1735481-3

Free Height Receptacle Conn: Board-Board, Vertical, 80, 0.8mm



TE Part #3-1903392-4

STD Temp Sig GRACE INERTIA Cap



TE Part #1-1649328-9

RTD34005



TE Part #1-2232784-2

GIC 7.92MM CONN HDR ASS'Y 2POS RED



TE Part #104196-5

20 SYSTEM 50 RCPT ASSY SRRA RED



Documents

Product Drawings

TUBULAR END SLEEVE

English

CAD Files

Customer View Model

ENG_CVM_1-966293-5_A1.3d_igs.zip

English

Customer View Model

ENG_CVM_1-966293-5_A1.3d_stp.zip

English

Customer View Model

ENG_CVM_1-966293-5_A1.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Wire Ferrules

English

WIRE END FERRULES

English