

D-SCE-1K-38-50-S1-9

✓ ACTIVE

TE Internal #: E52724-000

Printable Tubing, Ladder Printable Tubing Type, Fluid Resistant
Printable Tubing Grade, 3:1 Printable Tubing Shrink Ratio, White, 1
Prescore

[View on TE.com >](#)



Identification & Labeling > Printable Tubing > D-SCE FLUID RESISTANT SLEEVES



Printable Tubing Type: **Ladder**

Printable Tubing Grade: **Fluid Resistant**

Printable Tubing Shrink Ratio: **3:1**

Primary Product Color: **White**

Number of Prescores: **1**

[All D-SCE FLUID RESISTANT SLEEVES \(43\)](#)

Features

Product Type Features

Printable Tubing Type	Ladder
Printable Tubing Grade	Fluid Resistant

Body Features

Printable Tubing Shrink Ratio	3:1
Primary Product Color	White
Markers per Sleeve	2

Dimensions

Product Length	25 mm[1 in]
Supplied Inner Diameter	38.1 mm[1.5 in]
Recovered Inside Diameter	19 mm, 19.05 mm[.75 in][.752 in]
Compatible Cable Diameter Range	20.9 – 33. mm[.825 – 1.3 in]

Usage Conditions

Operating Temperature Range	-75 – 135 °C[-103 – 275 °F]
-----------------------------	-----------------------------

Operation/Application

Recommended Ribbon	See TE Document 411-121005 the Printer Product Ribbon Matrix
--------------------	--



Printer/Label Features

Recommended Printer	See TE Document 411-121005 the Printer Product Ribbon Matrix
Printer Technology	Thermal Transfer
Number of Prescores	1

Packaging Features

Packaging Quantity	1000
--------------------	------

Product Compliance

For compliance documentation, visit the product page on TE.com>



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



 TE Part # 1-2186500-1 T3212-PRINTER	 TE Part # 1-2186502-1 T3224-PRINTER	 TE Part # 1-2186503-1 T3224-SWARE-PRINTER	 TE Part # CP8122-000 T6112DS-PRINTER
 TE Part # 311292-000 TMS-RJS-RIBBON-4DSCE	 TE Part # F55931-000 1966-RIBBON	 TE Part # 1-2186501-1 T3212-SWARE-PRINTER	 TE Part # 1-2186538-1 RIB-1982-300-110-L-0
 TE Part # 1-2186549-1 RIB-1982-240-110-L-0-T200			

Customers Also Bought

 TE Part #2-325806-2 AMPOWER TERMINAL WO STUD HOLE	 TE Part #53853-2 AMPOWER KNIFE DISCONNECT	 TE Part #3045010001 RPS COMMERCIAL GRADE SLEEVES	 TE Part #53087 AMPOWER BUTT SPLICE LONG BARREL
 TE Part #405309-000 D-SCE FLUID RESISTANT SLEEVES	 TE Part #E67479-000 MP METALIZED POLYESTER LABELS	 TE Part #46757-3 HYP10 AMPPOWER 600MCM DIE SET	 TE Part #4-2317570-4 AV22 DPM 3A MOVING RING R&B 12V FL

Documents



Product Drawings

D-SCE-1K-38-50-S1-9

English

Datasheets & Catalog Pages

D-SCE Heat Shrink Identification Sleeves

English

IDENTIFICATION SELECTION GUIDE

English

Product Specifications

Product Specification

English

Instruction Sheets

Instruction Sheet (non U.S.)

English