



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2016 (169) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # 1-1600961-7
CONT 12-16 AWG PWR, MFBL PLATE



TE Part # 1-1600961-8
CONT 12-16 AWG PWR, STD PLATE

TE Part # 1-1600961-0
CONT MBXL 12-14 STD RE-REELED

TE Part # 1-1600961-1
CONT 12-16 AWG PWR, MFBL PLATE STRIP

TE Part # 1-1600961-2
CONT 12-16 AWG PWR, MFBL PLATE & FORMED

TE Part # 1-1600961-3
CONT 12-16 AWG PWR, MFBL LOOSE PIECE

TE Part # 1-1600961-4
CONT 12-16 AWG PWR, STD PLATED STRIP

TE Part # 1-1600961-5
CONT 12-16 AWG PWR, STD PLATED STRIP

TE Part # 1-1600961-6
CONT 12-16 AWG PWR, STD LOOSE PIECE

TE Part # 1600961-1
CONT 12-16AWG PWR BLANK STRIP

TE Part # 1600961-2
CONT 12-16AWG PWR PLATE STRIP

TE Part # 1600961-3
CONT 12-16AWG MFBL PLATE&FORM

TE Part # 1600961-4
CONT 12-16AWG MFBL LOOSE PIECE

TE Part # 1600961-5
CONT 12-16AWG STD BLANK STRIP

TE Part # 1600961-6
CONT 12-16AWG STD PLATED STRIP

TE Part # 1600961-7
CONT VERT BLKHEAD MT PWR 10AWG

TE Part # 1600961-8
CONT VERT BLKHEAD MT PWR 10AWG

TE Part # 1600961-9
CONT MBXL 12-14 MFBL RE-REELED


Customers Also Bought



TE Part #156666-1
PIDG FASTON RECPT QUICK
DISCONNECTS



TE Part #91531-1
CCII MTE AMPMODU MTE PIN REC
26-22 ASSY



TE Part #2-1658526-9
609-1630LF=FSKT IDC S 16 30AU



TE Part #3-1761606-3
IDC LOW PRO HDR 40P VERT LG LA



TE Part #1542618-2
XFP MSA SAN APPLICATION



TE Part #2-1445093-2
MICRO MNL HDR ASSY S/ROW AU LF



TE Part #1-1600961-8
CONT 12-16 AWG PWR, STD PLATE



TE Part #1-1600960-8
CONT 8-10 AWG PWR, STD PLATE &



TE Part #1565322-1
SHIELD FINGER 1608



TE Part #1217124-1
187 FASTON,PCB TAB,TNBR

Documents

Datasheets & Catalog Pages

Bottoming Dies

English

Instruction Sheets

Instruction Sheet (U.S.)

English