



HW

TE Internal #: E87437-000

HW, Standard Labels, Industrial Label, Die-Cut Label Style, High Tack Permanent Acrylic Adhesive, UL Listed Yes, Label Width 50.8 mm [2 in]

[View on TE.com >](#)

Identification & Labeling > Labels > Standard Labels > HW HIGH TACK WHITE POLYESTER LABELS



Label Type: **Industrial Label**

Label Style: **Die-Cut**

Label Adhesive Type: **High Tack Permanent Acrylic Adhesive**

UL Listed: **Yes**

Label Width: **50.8 mm [ 2 in ]**

[All HW HIGH TACK WHITE POLYESTER LABELS \(43\)](#)

Features

Product Type Features

Label Type	Industrial Label
------------	------------------

Body Features

Label Color	White
-------------	-------

Usage Conditions

Operating Temperature Range	-40 – 150 °C[-40 – 302 °F]
-----------------------------	----------------------------

Printer/Label Features

Number of Labels Across	1
Recommended Printer Ribbon	See Printer Ribbon Matrix
Label Style	Die-Cut
Label Width	50.8 mm[2 in]
Label Height	9.5 mm[.375 in]
Label Material	Polyester
Label Thickness	97 Micron

Industry Standards

UL Listed	Yes
-----------	-----



Packaging Features

Packaging Quantity	5000
Packaging Method	Roll

Other

Label Adhesive Type	High Tack Permanent Acrylic Adhesive
---------------------	--------------------------------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-2186500-1  
T3212-PRINTER



TE Part # 1-2186502-1  
T3224-PRINTER



TE Part # 1-2186503-1  
T3224-SWARE-PRINTER



TE Part # 1-2186501-1  
T3212-SWARE-PRINTER



Also in the Series

HW

Standard Labels(43)

Customers Also Bought

TE Part #1-794374-1  
SINGLE CIRCUIT MINI UMNL ASSY

TE Part #282858-6  
6P. TERMI-BLOK PCB MOUNT 90

TE Part #3-1437653-6  
6PCV-10-007=6PCV ASSEMBLY

TE Part #1658526-3  
609-1000MLF FEM SCKT,LEAD FREE

TE Part #2-1624246-0  
RSS3 22R 5% AMMO PK

TE Part #1-103906-0  
11 MTE HDR SRRA LATCH .100CL

TE Part #F17521-000  
HW HIGH TACK WHITE POLYESTER LABELS

TE Part #102142-9  
AMP-LATCH UNIVERSAL HEADERS

TE Part #6-106505-2  
D-Sub Receptacle Assembly: Right Angle, Shell Size 1, 2.74mm

TE Part #293652-1  
NECTOR S PCB CONN. ASSY. 90 DEG OUTLET

Documents

Product Drawings

HW-508095-5-9

English

Datasheets & Catalog Pages

HW High Tack White Polyester labels

English



IDENTIFICATION SELECTION GUIDE

English