




Identification & Labeling > Labels > Standard Labels > TN TAMPER EVIDENT POLYETHYLENE LABELS



Label Type: **Void & Tamper Evident Labels**

Label Style: **Die-Cut**

Label Adhesive Type: **Rubber Adhesive**

UL Listed: **Yes**

Label Width: **50.8 mm [2 in]**

[All TN TAMPER EVIDENT POLYETHYLENE LABELS \(17\)](#)

Features

Product Type Features

Label Type	Void & Tamper Evident Labels
------------	------------------------------

Body Features

Label Color	White
-------------	-------

Usage Conditions

Operating Temperature Range	-40 – 80 °C[-40 – 176 °F]
-----------------------------	---------------------------

Printer/Label Features

Number of Labels Across	1
Recommended Printer Ribbon	See Printer Ribbon Matrix
Label Style	Die-Cut
Label Width	50.8 mm[2 in]
Label Height	25.4 mm[1 in]
Label Material	Polyethylene
Label Thickness	48 Micron

Industry Standards

UL Listed	Yes
-----------	-----



Packaging Features

Packaging Quantity	5000
Packaging Method	Roll

Other

Label Adhesive Type	Rubber Adhesive
---------------------	-----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-2186500-1
T3212-PRINTER



TE Part # 1-2186502-1
T3224-PRINTER



TE Part # 1-2186503-1
T3224-SWARE-PRINTER



TE Part # 1-2186501-1
T3212-SWARE-PRINTER



Also in the Series

Raychem RTD

Automotive Headers(1)

RF Connectors(31)

RTD Probes & Assemblies(2)

Standard Labels(17)

Wire-to-Board Connector Contacts(1)

Customers Also Bought

TE Part #0462-209-16141
DEUTSCH SOLID CONTACTS

TE Part #1-1337541-0
BNC Ins Str PCB Skt 50Ohm White

TE Part #W6P
DEUTSCH DT WEDGELOCKS

TE Part #114017-ZZ
DEUTSCH SEALING PLUGS

TE Part #1241050-5
2x5P MOD II BREAK AWAY HDR,SMD,
BLISTER

TE Part #1-480698-0
02P UMNL PLUG HSG NATL

TE Part #1-1775333-6
0.5mm FPC Connectors

Documents

- Datasheets & Catalog Pages
- Tamper proof destructible polyethylene labels
- English
- IDENTIFICATION SELECTION GUIDE
- English

