




Relays, Contactors & Switches > Relays > Relay Accessories, Sockets & Clips



Relay Accessory, Socket & Clip Product Type: **Socket**
Relay Accessory, Socket & Clip Socket Type: **DIN Rail Mount**
Grounding Provision: **Without**
Relay Accessory, Socket & Clip Body Material: **Nylon**
Relay Accessory, Socket & Clip For Use With: **KUP Relays**

Features

Product Type Features

Terminal Configuration	Screw
Relay Accessory, Socket & Clip Product Type	Socket
Relay Accessory Type	Socket

Configuration Features

Grounding Provision	Without
---------------------	---------

Body Features

Relay Accessory, Socket & Clip Body Material	Nylon
--	-------

Contact Features

Terminal Length	69.96 mm[.212 in]
Contact Plating Material	Tin
Contact Base Material	Spring Brass
Relay Accessory, Socket & Clip Socket Type	DIN Rail Mount
Pole Configuration	4

Termination Features



Number of Pins	14
----------------	----

Mechanical Attachment

Relay Accessory, Socket & Clip Mounting Type	Panel, Rail
--	-------------

Operation/Application

Relay Accessory, Socket & Clip For Use With	KUP Relays
---	------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2013 (144) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



 TE Part # 5-1393118-0 KUP-17D19-24=KU	 TE Part # 3-1393159-9 20C254=SPRING,HOLD-DOWN,KUP,0	 TE Part # 6-1393118-0 KUP-5A15-24=KU	 TE Part # 6-1393118-1 KUP-5A15-240=KU
 TE Part # 6-1393118-6 KUP-5D15-12=KU	 TE Part # 6-1393118-7 KUP-5D15-24=KU	 TE Part # 4-1393118-2 KUP-17A19-120=KU	 TE Part # 4-1393118-3 KUP-17A19-24=KU
 TE Part # 4-1393118-9 KUP-17D19-12=KU	 TE Part # 5-1393118-9 KUP-5A15-120=KU	 TE Part # 5-1423996-5 KUP-17A39-120=RELAY,4C,AGCDO, QC.110,LAMP	 TE Part # 4-1393118-8 KUP-17D19-110=KU
 TE Part # 6-1423960-9 KUP-17D19-48=RELAY,4C,AGCDO, QC.110,DUST	 TE Part # 1-1423960-2 KUP-17D19F-110=RELAY,4C,AGCDO, GOLD FLASH		

Also in the Series | **Potter & Brumfield KUP**


 Power Relays(155)	 Relay Accessories, Sockets & Clips(12)
--	---

Customers Also Bought







TE Part #2-1423159-3
7012PC=RLY,STD,ON,2P,125VDC,15



TE Part #1419111-5
24A071=CLIP,SKT,ASSY,W/SCW



TE Part #1393143-6
27E122=SOCKET,KRP,8,SCW,PLES



TE Part #2-1419106-3
27E891=SOCKET,KRPA,8,OCTAL,POL



TE Part #1-1423159-9
7012PB=RLY,STD,ON,2P,125VDC, 5




TE Part #2-1423162-9
7022BK=RLY,STD,OFF,M2P,240VAC,




TE Part #1423155-3
GPC=RELAY,48VDC



TE Part #YDTS26W13-35PNV001
D38999: Straight Plug, 13-35 Insert



TE Part #1437536-3
DIP Socket: Standard, Stamped & Formed, Closed, Gold



TE Part #1437536-5
DIP Socket: Standard, Screw Machine, Closed, Gold

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-1419106-2_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-1419106-2_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-1419106-2_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

KU Sockets & Accessories

English

Industrial Relays Quick Reference Guide

English



Industrial Relays Quick Reference Guide

Japanese

Industrial Relays Quick Reference Guide

Product Specifications

Definitions, Handling, Processing, Testing and Use of Relays

English