



WP

TE Internal #: E98371-000

WP, Standard Labels, Industrial Label, Die-Cut Label Style,  
Permanent Acrylic Adhesive, UL Listed Yes, Label Width 47.8 mm  
[1.88 in]

[View on TE.com >](#)

Identification & Labeling > Labels > Standard Labels > WP WHITE POLYESTER LABELS



Label Type: **Industrial Label**

Label Style: **Die-Cut**

Label Adhesive Type: **Permanent Acrylic Adhesive**

UL Listed: **Yes**

Label Width: **47.8 mm [ 1.88 in ]**

[All WP White Polyester Labels \(29\)](#)

Features

Product Type Features

Label Type	Industrial Label
------------	------------------

Body Features

Label Color	White
-------------	-------

Usage Conditions

Operating Temperature Range	-40 – 150 °C[-40 – 302 °F]
-----------------------------	----------------------------

Printer/Label Features

Number of Labels Across	1
Recommended Printer Ribbon	See Printer Ribbon Matrix
Label Style	Die-Cut
Label Width	47.8 mm[1.88 in]
Label Height	17.5 mm[.69 in]
Label Material	Polyester
Label Thickness	72 Micron

Industry Standards

UL Listed	Yes
-----------	-----



Packaging Features

Packaging Quantity	5000
Packaging Method	Roll

Other

Label Adhesive Type	Permanent Acrylic Adhesive
---------------------	----------------------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # 1-2186500-1  
T3212-PRINTER



TE Part # 1-2186502-1  
T3224-PRINTER



TE Part # 1-2186503-1  
T3224-SWARE-PRINTER



TE Part # 1-2186501-1  
T3212-SWARE-PRINTER

Also in the Series | WP



Standard Labels(29)

Customers Also Bought



TE Part #1473005-1  
DDR2 SO DIMM Sockets



TE Part #1-178141-2  
DYNAMIC 3100 HDR ASSY



TE Part #1-1415898-4  
PCB Power Relay: 16 Amp, Inrush




TE Part #1241152-3  
3P HV100 REC. CON, SMD, GOLD, BLISTER




TE Part #1-292227-5  
MINI COMMON TERMINATION HEADERS



TE Part #1241050-5  
2x5P MOD II BREAK AWAY HDR,SMD, BLISTER



TE Part #1-215307-3  
2X13P HV100 REC CON. TE, 7.0MM



TE Part #1-84952-4  
1MM FPC HORZ.BTTM CONT.ASS.14P



TE Part #1617156-2  
MGSCD-12 = MGSD .100 GRID DIOD



TE Part #YACT20MF32ANV00100  
SQUARE FLANGE RECEPTACLE



Documents

Product Drawings

WP-478175-5-9

English

Datasheets & Catalog Pages

WP White Polyester labels

English

IDENTIFICATION SELECTION GUIDE

English