




Relays, Contactors & Switches > Relays > Relay Accessories, Sockets & Clips



Relay Accessory, Socket & Clip Product Type: **Socket**  
Relay Accessory, Socket & Clip Socket Type: **DIN Rail Mount**  
Grounding Provision: **Without**  
Relay Accessory, Socket & Clip Body Material: **Glass-Filled Polyester**  
Relay Accessory, Socket & Clip For Use With: **K10 Relays**

Features

Product Type Features

|                                             |                            |
|---------------------------------------------|----------------------------|
| Terminal Configuration                      | Screw, DIN Rail Snap-Mount |
| Relay Accessory, Socket & Clip Product Type | Socket                     |
| Relay Accessory Type                        | Socket                     |

Configuration Features

|                     |         |
|---------------------|---------|
| Grounding Provision | Without |
|---------------------|---------|

Body Features

|                                              |                        |
|----------------------------------------------|------------------------|
| Relay Accessory, Socket & Clip Body Material | Glass-Filled Polyester |
|----------------------------------------------|------------------------|

Contact Features

|                                            |                |
|--------------------------------------------|----------------|
| Terminal Length                            | 26.31 mm       |
| Contact Plating Material                   | Tin            |
| Contact Base Material                      | Spring Brass   |
| Relay Accessory, Socket & Clip Socket Type | DIN Rail Mount |
| Pole Configuration                         | 2              |



Termination Features

|                |   |
|----------------|---|
| Number of Pins | 8 |
|----------------|---|

Mechanical Attachment

|                                              |                     |
|----------------------------------------------|---------------------|
| Relay Accessory, Socket & Clip Mounting Type | DIN Rail Snap Mount |
|----------------------------------------------|---------------------|

Operation/Application

|                                             |            |
|---------------------------------------------|------------|
| Relay Accessory, Socket & Clip For Use With | K10 Relays |
|---------------------------------------------|------------|

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                               |
|-----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                     |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                     |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                       |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2021 (211)<br>Candidate List Declared Against: JAN 2021 (211)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                           |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                  |

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



|                                                                                                                                            |                                                                                                                                             |                                                                                                                                               |                                                                                                                                               |
|--------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------|
|  <p>TE Part # 5-1393144-7<br/>K10P-11D15-24=K10/K20</p>   |  <p>TE Part # 4-1393144-0<br/>K10P-11A15-120=K10/K20</p>   |  <p>TE Part # 3-1393144-9<br/>K10P-11A15-12=K10/K20</p>    |  <p>TE Part # 4-1393144-1<br/>K10P-11A15-24=K10/K20</p>    |
|  <p>TE Part # 5-1393144-5<br/>K10P-11D15-12=K10/K20</p>   |  <p>TE Part # 4-1393144-2<br/>K10P-11A15-240=K10/K20</p>   |  <p>TE Part # 4-1393144-4<br/>K10P-11A15-6=K10/K20</p>     |  <p>TE Part # 5-1393144-9<br/>K10P-11D15-48=K10/K20</p>    |
|  <p>TE Part # 6-1393144-0<br/>K10P-11D15-6=K10/K20</p>  |  <p>TE Part # 5-1393144-4<br/>K10P-11D15-110=K10/K20</p> |  <p>TE Part # 5-1393144-6<br/>K10P-11D15-120=K10/K20</p> |  <p>TE Part # 2-1393144-1<br/>K10L-11A15-120=K10/K20</p> |
|  <p>TE Part # 4-1393144-3<br/>K10P-11A15-48=K10/K20</p> |  <p>TE Part # 1393145-4<br/>K10P-7AT5-120=K10/K20</p>    | <p>TE Part # 5-1393159-1<br/>20C426=SPRING,HOLD-DOWN,K10,.0</p>                                                                               |                                                                                                                                               |

Also in the Series | **Potter & Brumfield K10**

|                                                                                                             |                                                                                                                                      |
|-------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------|
|  <p>Power Relays(27)</p> |  <p>Relay Accessories, Sockets &amp; Clips(3)</p> |
|-------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------|

Customers Also Bought



TE Part #1-66361-2  
TYPE III CONTACTS LP

TE Part #7-66504-0  
D-Sub Conn Contacts: Socket, Phosphor Bronze, Signal, Size 20

TE Part #1546413-3  
ETHERNET RJ-45 BLKHD PASSTHRU

TE Part #1-66105-8  
III+ SKT,24-20,30AU/FL,SMPACK

TE Part #1-770250-0  
UMN L II PIN SN/AUNI/BR LP20-14

TE Part #1-66103-7  
III+ PIN,24-20,15AU/FL,SMPACK

TE Part #1419111-6  
24A110=TRACK,MOUNTING

TE Part #1776089-1  
CMC SERIES 4

TE Part #1-87499-9  
11 MODIV HSG SR MRKD .100CL

TE Part #1-1437558-0  
MTA106D=(MSTA) SWITCH TOGGLE S

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_2-1419106-7\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_2-1419106-7\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_2-1419106-7\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

K10 Sockets & Accessories

English

Industrial Relays Quick Reference Guide

English



Industrial Relays Quick Reference Guide

Japanese

Industrial Relays Quick Reference Guide

Product Specifications

Definitions, Handling, Processing, Testing and Use of Relays

English