



Identification & Labeling > Printable Tubing > ZHD-SCE LFH & FLUID RESISTANT SLEEVES



Printable Tubing Type: **Ladder**
Printable Tubing Grade: **Low Fire Hazard**
Printable Tubing Shrink Ratio: **2:1**
Primary Product Color: **White**
Markers per Sleeve: **1**

[All ZHD-SCE LFH & FLUID RESISTANT SLEEVES \(88\)](#)

Features

Product Type Features

Printable Tubing Type	Ladder
Printable Tubing Grade	Low Fire Hazard

Body Features

Printable Tubing Shrink Ratio	2:1
Primary Product Color	White
Markers per Sleeve	1

Dimensions

Product Length	50 mm[2 in]
Supplied Inner Diameter	12.7 mm[.5 in]
Recovered Inside Diameter	6.35 mm[.25 in]
Compatible Cable Diameter Range	6.99 – 10.79 mm[.275 – .425 in]

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Recommended Ribbon	See TE Document 411-121005 the Printer Product Ribbon Matrix
--------------------	--



Printer/Label Features

Recommended Printer	See TE Document 411-121005 the Printer Product Ribbon Matrix
Printer Technology	Thermal Transfer

Packaging Features

Packaging Quantity	250
--------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-2186500-1
T3212-PRINTER

TE Part # 1-2186502-1
T3224-PRINTER

TE Part # 1-2186503-1
T3224-SWARE-PRINTER

TE Part # CP8122-000
T6112DS-PRINTER

TE Part # 1-2186501-1
T3212-SWARE-PRINTER

Also in the Series | ZHD-SCE

Printable Tubing(88)

Customers Also Bought

TE Part #2-323136-1
SOLIS SPDFLG 22-16COM22-18MIL6

TE Part #2329384-2
PB OFF/ON FC RED M1 TERM IP68 500MM L

TE Part #338705-000
FLTWC0311-22-3

TE Part #3-641240-7
Nylon Gold Plated Receptacle: 2.54 mm, No Mating Alignment, MTA 100

TE Part #YDTS26F15-05PAV001
Straight Plug: D38999, 15-05 Insert, Electroless Nickel Plating


TE Part #EC9880-000
ZHD-SCE LFH & FLUID RESISTANT SLEEVES

TE Part #1060875-2
MCX CABLE PLUG, CRIMP ATTACH

TE Part #1375875-3
PLUG HSG,10POS,0.8MM MICRO INT



TE Part #2170753-5
CAGE ASSY, QSFP28 1X1, GASKET, HS



TE Part #517387-000
55A0821-22-9/96CS2275

Documents

Product Drawings

ZHD-SCE-12.7-50-9

English

Datasheets & Catalog Pages

TTDS for ZHD-SCE, LOW FIRE HAZARD, DIESEL RESISTANT

English

Product Specifications

Product Specification

English