



WV

TE Internal #: F51616-000

WV, Standard Labels, Industrial Label, Die-Cut Label Style, High Tack Permanent Acrylic Adhesive, UL Listed No, Label Width 38.1 mm [1.5 in]

[View on TE.com >](#)

Identification & Labeling > Labels > Standard Labels > WV HIGH TACK WHITE VINYL LABELS



Label Type: **Industrial Label**

Label Style: **Die-Cut**

Label Adhesive Type: **High Tack Permanent Acrylic Adhesive**

UL Listed: **No**

Label Width: **38.1 mm [1.5 in]**

[All WV HIGH TACK WHITE VINYL LABELS \(25\)](#)

Features

Product Type Features

Label Type	Industrial Label
------------	------------------

Body Features

Label Color	White
-------------	-------

Usage Conditions

Operating Temperature Range	-40 – 80 °C[-40 – 176 °F]
-----------------------------	---------------------------

Printer/Label Features

Number of Labels Across	2
Recommended Printer Ribbon	See Printer Ribbon Matrix
Label Style	Die-Cut
Label Width	38.1 mm[1.5 in]
Length of Label Roll	38.1 m[1.5 ft]
Label Height	19.1 mm[.75 in]
Label Material	Vinyl Film
Label Thickness	75 Micron

Industry Standards



UL Listed	No
-----------	----

Packaging Features

Packaging Quantity	5000
Packaging Method	Roll

Other

Label Adhesive Type	High Tack Permanent Acrylic Adhesive
---------------------	--------------------------------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-2186500-1
T3212-PRINTER

TE Part # 1-2186502-1
T3224-PRINTER

TE Part # 1-2186503-1
T3224-SWARE-PRINTER

TE Part # 1-2186501-1
T3212-SWARE-PRINTER

Also in the Series | WV

Standard Labels(7)

Customers Also Bought

TE Part #182651-1
CPC EMEA

TE Part #1-640507-0
02P MR II CAP HSG

TE Part #172338-1
MINI UMNL PLUG HOUSING 4P

TE Part #1-213781-0
CPC RCPT ASSY SIZE 23-19,S/L

TE Part #145831-000
Low Profile Heat Shrink Boots: Blow Mold, Lipped, Right Angle

TE Part #YDTS26W09-98SCC001
D38999: Straight Plug, 09-98 Insert

TE Part #104583-1
64 LEVEL V COVER .125

TE Part #1385638-2
HDM SAPR176F2200 K

TE Part #1803384-2
CRIMPER, INSULATION F

TE Part #2-1532023-9
095-0615-2030=MCDR3-B-51PS



Documents

Product Drawings

WV-381191-5-9

English

Datasheets & Catalog Pages

EET V-9

English

IDENTIFICATION SELECTION GUIDE

English