

DWP-125-1-9-2IN

✓ ACTIVE

Raychem | Raychem DWP-125

TE Internal #: F65959-000

Raychem DWP-125, Heat Shrink Tubing, White, Dual Wall Type,  
25.4 Expanded Inside Diameter (Min) 1 Expanded Inside Diameter  
(Min)

[View on TE.com >](#)



Heat Shrink Tubing > Dual Wall DWP-125 Spool HS Tubing



Primary Product Color: **White**

Wall Type: **Dual**

Expanded Inside Diameter (Min): **25.4 mm [ 1 in ]**

Recovered Inside Diameter (Max): **8.1 mm [ .32 in ]**

Shrink Ratio: **3:1**

[All Dual Wall DWP-125 Spool HS Tubing \(57\)](#)

Features

Product Type Features

Product Family	DWP-125
Wall Type	Dual

Electrical Characteristics

Voltage (Max)	.6 kV
---------------	-------

Body Features

Fluid Type	Hydraulic Fluid, Lubricating Oil, Water
Primary Product Color	White
Shrink Ratio	3:1
Primary Product Material	Irradiated Modified Polyolefin
Flexibility	Flexible

Dimensions

Recovered Wall Thickness (Tolerance)	2.54 mm[.1 in]
Cut Length	50.8 mm[2 in]
Expanded Inside Diameter (Min)	25.4 mm[1 in]
Recovered Inside Diameter (Max)	8.1 mm[.32 in]
Heat Shrink Tubing Size Range	8.1 – 25.4 mm[.32 – 1 in]



Usage Conditions

Shrink Temperature (Min)	80 °C
Heat Shrink Tubing Flammability	Flame-Retardant
Operating Temperature Range	-40 – 110 °C
Heat Shrink Tubing Resistance	Fluids
Recovery Temperature	125 °C

Product Availability

Applicable Region	Global
-------------------	--------

Packaging Features

Packaging Method	Box
------------------	-----

Other

Meets Low Outgassing Requirements	No
Product Source	US

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

<p>TE Part # 2280355-1 220 V MODEL 17</p>	<p>TE Part # 2280355-3 110 V MODEL 17</p>	<p>TE Part # 2280355-4 110 V MODEL 17 REVERSE</p>	<p>TE Part # 2326489-1 MODEL 105 TUNNEL OVEN, 36" ENTRY, STAND A</p>
<p>TE Part # 2375310-1 XB17 Belt Heater, 220V</p>	<p>TE Part # 2375310-2 XB17 Belt Heater, 110V</p>	<p>TE Part # 2375320-1 XB19 Belt Heater, STD</p>	<p>TE Part # 2375320-2 XB19 Belt Heater, 150mm (6") Version</p>
<p>TE Part # 955018-000 CLTEQ-M105-TUNNEL-OVEN</p>	<p>TE Part # 714529-000 CLTEQ-M19-BELT-HTR</p>	<p>TE Part # CJ1047-000 VBH-1-BED-HTR-220V-3WR</p>	

Also in the Series | Raychem DWP-125

Heat Shrink Tubing(86)

Customers Also Bought



TE Part #1-480705-0  
06P UMNL CAP HSG NATL



TE Part #1-880488-2  
FASTON 187 HOUSING RECEPTACLE



TE Part #350536-1  
UMNL SOK 20-14 .0126 PTPBR



TE Part #1-880488-4  
FASTON 187 HOUSING RECEPTACLE



TE Part #1-881623-1  
FASTON 187 REC 0.5-1.0MM2 0.32X13.97 BR



TE Part #1241981-5  
STANDARD TIMER HOUSING



TE Part #1534073-4  
MULTIFIT MK2 ASSY4P,AR



TE Part #2-1534073-4  
1-4 POS. MULTIFIT MK2 ASSY



TE Part #2029387-1  
04P UMNL SHORT LATCH PLUG V0



TE Part #CP4925-000  
ES2000-NO.3-B8-0-60MM-SH

Documents

Product Drawings

DWP-125-1-9-2IN

English

Datasheets & Catalog Pages

DWP-125 Pages from 9-1773447-9

English

Application Tooling for Raychem Heat Shrink Product

English

Flexible, Flame-Retardant, Adhesive-lined, Polyolefin Heat-Shrinkable Tubing

English

Measuring\_Single\_Wall\_Tubing

English

Selecting\_Correct\_Tubing

English

Product Specifications

Quality Specification

English

DWP-125-1-9-2IN

Raychem DWP-125, Heat Shrink Tubing, White, Dual Wall Type, 25.4 Expanded Inside Diameter (Min) 1 Expanded Inside Diameter (Min)

