



QSFP/QSFP+

TE Internal #: 2214574-6
QSFP/QSFP+, QSFP/QSFP+/zQSFP+, Cage Assembly with Integrated Connector, Port Matrix Configuration 2 x 2, Elastomeric Gasket, Included Lightpipe

[View on TE.com >](#)

Connectors > Pluggable IO Connectors & Cages > QSFP/QSFP+/zQSFP+



Pluggable I/O Product Type: **Cage Assembly with Integrated Connector**
Port Matrix Configuration: **2 x 2**
EMI Containment Feature Type: **Elastomeric Gasket**
Included Lightpipe: **Yes**
Enhancements: **Standard**

Features

Product Type Features

Form Factor	QSFP+
Cage Type	Stacked
Pluggable I/O Product Type	Cage Assembly with Integrated Connector
Connector System	Cable-to-Board
Sealable	Yes
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Port Matrix Configuration	2 x 2
Number of Ports	4
Lightpipe Configuration	Inner Left Indicator Down
Number of Rear EONs per Port Column	0
Number of Positions	152

Electrical Characteristics

Data Rate (Max)	14 Gb/s
-----------------	---------

Contact Features

Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Thickness	.76 µm[30 µin]



Contact Underplating Material	Tin
-------------------------------	-----

PCB Contact Termination Area Plating Material	Gold
---	------

Termination Features

Termination Method to Printed Circuit Board	Through Hole - Press-Fit
---	--------------------------

Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------

Housing Features

Cage Material	Nickel Silver
---------------	---------------

Centerline (Pitch)	.8 mm[.032 in]
--------------------	----------------

Dimensions

PCB Thickness (Recommended)	1.57 mm[.062 in]
-----------------------------	------------------

Tail Length	2 mm[.079 in]
-------------	---------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Heat Sink Compatible	No
----------------------	----

For Use With Pluggable I/O Products	QSFP Cable Assembly, QSFP MSA Compatible Transceiver
-------------------------------------	---

Pluggable I/O Applications	SFP+ Stacked Belly-to-Belly
----------------------------	-----------------------------

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Box & Tray
------------------	------------

Other

EMI Containment Feature Type	Elastomeric Gasket
------------------------------	--------------------

Included Lightpipe	Yes
--------------------	-----

Enhancements	Standard
--------------	----------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Yet Reviewed
------------------------------	------------------



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Not Yet Reviewed
Halogen Content	Out of Scope - excluded from Halogen requirements
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # CAT-C11-H501114
QSFP to QSFP I/O Cable Assembly: 30 AWG



TE Part # CAT-C11-H50111
QSFP-Four SFP+ I/O Cable Assembly 30 AWG



TE Part # 2110819-1
QSFP+ Enh EVERCLEAR PT Conn



TE Part # 1888810-2
EMI/Dust Cover,XFP And QSFP



TE Part # CAT-C11-H5011
QSFP-Four SFP+ I/O Cable Assembly 28 AWG



TE Part # CAT-C11-H5011142
QSFP to QSFP I/O Cable Assembly: 33 AWG



TE Part # 2053638-5
C/A, QSFP, 5M, P1-P2, UNEQUALIZED



TE Part # 1-2220639-0
QSFP TO QSFP, ACTIVE, 28AWG, 10M



TE Part # 1-2220639-3
QSFP TO QSFP, ACTIVE, 28AWG, 13M



TE Part # 2053638-4
C/A, QSFP, 4M, P1-P2, UNEQUALIZED



TE Part # CAT-C11-H501
QSFP-Four SFP+ I/O Cable Assembly 26 AWG



TE Part # 2202165-4
QSFP TO QSFP, 26AWG, FDR, 4.0 METER



TE Part # 2202165-5
QSFP TO QSFP, 26AWG, FDR, 5.0 METER



TE Part # 2821033-8
QSFP TO [4]SFP+, 28G, 1M, 33AWG




TE Part # 2202165-1
QSFP TO QSFP, 30AWG, FDR, 1.0 METER



TE Part # 2202165-3
QSFP TO QSFP, 28AWG, FDR, 3.0 METER


Also in the Series | QSFP/QSFP+



Heat Sinks(1)



Pluggable I/O Cable Assemblies(33)



QSFP/QSFP+/zQSFP+(168)


Customers Also Bought



TE Part #2170872-1
Hard Metric Male Connector: Traditional Backplane, Mezzanine, 2mm



TE Part #2-1658063-3
MSB0.80PL5ASY120FL,-,10,-TY



TE Part #1934937-1
Tinman 5pr 10col open hdr assy



TE Part #2-1734774-1
PCI EXP 3.1L 98 POS WHT 30u




TE Part #2007850-1
IMP100S,H,V5P10C,UG,DEW46,4,5



TE Part #2132423-1
IMP100O,R,RA3P6C,RG,39




TE Part #2204400-4
MULTI-BEAM HD R/A REC. 15S+3P+3P+15S



TE Part #3-1775099-2
ATX PWR CONN 1 BDLK 8 POS



TE Part #6-1658043-2
[MSB0.80RC-ASY080FL,GP,F,-TR](#)



TE Part #2-2204910-5
[MBXLE R/A HEADER 4HDP + 92S + 4HDP](#)

Documents

Product Drawings

2X2 QSFP CAGE AND PT CONNECTOR ASSEMBLY

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_2214574-6_B.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2214574-6_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2214574-6_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English