



Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Cadmium oxide (10% in contact) Article Safe Usage Statements: Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Customers Also Bought




TE Part #103669-1
02 MTE HDR SRST LATCH W/HLDWN



TE Part #1871058-1
PCI EXPRESS CONN. EON TYPE, 36P, L=2.0



TE Part #1888631-2
Cage Assy SAN Hsink QSFP Thru Bezel




TE Part #146845-1
BATT INT,KEYLESS,5P,7.2V



TE Part #1888566-1
IMJ,1X1,PNL GRD,LED(YG/YG), SN



TE Part #6-1879211-6
CPF 0402 8K25 0.1% 25PPM 5K RL




TE Part #103669-2
03 MTE HDR SRST LATCH W/HLDWN



TE Part #1879021-9
SMW3 R22 5%



TE Part #1-2176369-8
RQ 0603 60R4 0.1% 10PPM 5K RL



TE Part #103669-5
06 MTE HDR SRST LATCH W/HLDWN

Documents

Datasheets & Catalog Pages

Industrial Relays Quick Reference Guide

English

T92 Two-Pole, 30 Amp, PC Board or Panel Mount Relay

English

Industrial Relays Quick Reference Guide

Japanese

Industrial Relays Quick Reference Guide

Product Specifications

Definitions, Handling, Processing, Testing and Use of Relays

English