




Connectors > Pluggable IO Connectors & Cages > SFP/SFP+/zSFP+ > zSFP+ Stacked Cage Assembly: EMI Spring



Pluggable I/O Product Type: **Cage Assembly with Integrated Connector**

Data Rate (Max): **32 Gb/s**

EMI Containment Feature Type: **External Springs**

Pluggable I/O Applications: **zSFP+ Thermally Enhanced**

Included Lightpipe: **No**

[All zSFP+ Stacked Cage Assembly: EMI Spring \(45\)](#)

Features

Product Type Features

Form Factor	zSFP+ Stacked (SFP28)
Cage Type	Stacked
Pluggable I/O Product Type	Cage Assembly with Integrated Connector
Connector System	Cable-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Port Matrix Configuration	2 x 12
Number of Ports	24
Number of Positions	24

Electrical Characteristics

Data Rate (Max)	32 Gb/s
-----------------	---------

Contact Features

--	--



Tail Plating Material	Tin
Contact Mating Area Plating Thickness	.76 μm[29.92 μin]

Termination Features

Termination Method to Printed Circuit Board	Through Hole - Press-Fit
---	--------------------------

Mechanical Attachment

PCB Mounting Style	Through Hole - Press-Fit
Connector Mounting Type	Board Mount

Housing Features

Cage Material	Nickel Silver Alloy
Centerline (Pitch)	4.9 mm[.193 in]

Dimensions

PCB Thickness (Recommended)	1.5 mm[.059 in]
Tail Length	1.8 mm[.07 in]

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Heat Sink Compatible	No
For Use With Pluggable I/O Products	zSFP+ Cable Assembly
Pluggable I/O Applications	zSFP+ Thermally Enhanced
Circuit Application	Signal

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Tray
------------------	------

Other

EMI Containment Feature Type	External Springs
Included Lightpipe	No
Comment	With insulating tape.

Product Compliance

For compliance documentation, visit the product page on TE.com>



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2016 (169) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # CAT-C11-N490333
QSFP28-Four SFP+ Cable Assembly:
30 AWG



TE Part # CAT-C11-N490325
QSFP28-Four SFP+ Cable Assembly:
26 AWG



TE Part # CAT-C11-N4901142
SFP28 to SFP28 Cable Assembly: 32
AWG



TE Part # CAT-C11-N4901114
SFP28 to SFP28 Cable Assembly: 30
AWG





TE Part # CAT-C11-N49011
SFP28 to SFP28 Cable Assembly: 26 AWG



TE Part # CAT-Q17-N49011
QSFP56-Four SFP56 Cable Assembly: 30 AWG



TE Part # CAT-Q17-N490333
QSFP56-Four SFP56 Cable Assembly: 26 AWG



TE Part # CAT-C11-G28037
SFP56 to SFP56 Cable Assembly: 30 AWG



TE Part # CAT-C11-G28
SFP56 to SFP56 Cable Assembly: 26 AWG



TE Part # 2821262-1
SFP28 DIRECT ATTACH CA, 0.5M, 33AWG



TE Part # 4-2334985-2
SFP56 DIRECT ATTACH CA, 1M, 32AWG



TE Part # CAT-C11-N490111
SFP28 to SFP28 Cable Assembly: 28 AWG



TE Part # 2821262-2
SFP28 DIRECT ATTACH CA, 1.0M, 33AWG



TE Part # 2821262-3
SFP28 DIRECT ATTACH CA, 1.5M, 33AWG



TE Part # 2821262-4
SFP28 DIRECT ATTACH CA, 2.0M, 33AWG

Customers Also Bought



TE Part #2328118-3
LUMAWISE ENDURANCE N OPEN CAP ASSEMBLY



TE Part #2132529-3
IMP100S,H,V3P6C,LG,REW39,5.5



TE Part #1470108-6
AMP HPI 2.0MM HEADERS




TE Part #YDTS26T23-53SNV001
D38999: Straight Plug, 23-53 Insert



TE Part #1734100-3
Champ050 series,30pos,Au over PdNi



TE Part #1734101-3
Champ050 series,30pos,Au over PdNi



TE Part #1757256-1
SMPM FEMALE BULLET ADAPTER



TE Part #1934949-1
Tinman 5pr 8col vert recpt 15mm stack



TE Part #2007808-2
IMP100S,H,V4P10C,LG,OEW46,4.9



TE Part #2110570-1
SFP+ 1x4 Cage Assembly Square Light Pipe

Documents

Product Drawings

ZSFP+ STACKED 2X12 RCPT ASSY, AIRFLOW

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2301210-2_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2301210-2_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2301210-2_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

zSFP+ Interconnect Brochure

English

Product Specifications

Application Specification

English

Application Specification

English