

3SBH1149A2

✓ ACTIVE

CII | CII 3SBH Relay

TE Internal #: 1-1617076-6

CII 3SBH Relay, 1/5-Size Relays, 1/5-Size Relay Contact


Arrangement 4 Form C, 4PDT, 4 C/O, 12VDC 1/5-Size Relay Input

Voltage

[View on TE.com >](#)



Relays, Contactors & Switches > Relays > Mil-Aero Relays > 1/5-Size Relays



1/5-Size Relay Contact Arrangement: **4 Form C, 4PDT, 4 C/O**

1/5-Size Relay Input Voltage: **12 VDC**

Coil Suppression Diode: **Without**

1/5-Size Relay Contact Current Rating: **2 A**

1/5-Size Relay Coil Voltage Rating: **12 VDC**

Features

Product Type Features

Enclosure Type	Hermetically Sealed
Relay Type	Military/Aerospace High Performance
Coil Latching	Without
Product Type	Relay
MOSFET Driver	Without

Configuration Features

Transistor Driver	Without
-------------------	---------

Electrical Characteristics

Actuating System	DC
Vibration	30G's, 10 – 3000Hz
Coil Magnetic System	Non-Polarized, Monostable
Shock	75G's, 6ms
Coil Power Measurement	Milliwatts
Coil Polarity Protection Diode	Without
1/5-Size Relay Input Voltage	12 VDC
Coil Suppression Diode	Without
1/5-Size Relay Coil Voltage Rating	12 VDC



1/5-Size Relay Coil Resistance	115 Ω
1/5-Size Relay Coil Power Rating (DC)	1252 mW

Contact Features

1/5-Size Relay Contact Arrangement	4 Form C, 4PDT, 4 C/O
1/5-Size Relay Contact Current Rating	2 A

Termination Features

Termination Type	PC Pins
------------------	---------

Mechanical Attachment

1/5-Size Relay Mounting Type	Printed Circuit Board
------------------------------	-----------------------

Usage Conditions

Operating Temperature Range	-65 – 125 $^{\circ}\text{C}$
-----------------------------	------------------------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not lead free process capable

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling



based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts

TE Part # 2-1617072-6
3SBC1517A2 = M39016/13-056M

Also in the Series | CII 3SBH Relay

1/5-Size Relays(22)

Customers Also Bought

TE Part #1617146-3
JMGACD-12M = M39016/18-034M

TE Part #2-1617146-0
JMGACD-6M = M39016/18-032M

TE Part #YDTS20W17-35AAV001
D38999: Square Flange, 17-35 insert

TE Part #1617014-8
3SAT1347A2 = M5757/13-130

TE Part #5-1618071-6
253-5X=WILMAR OVER
/UNDervOLTAG

TE Part #387778-000
44A1111-22-90-9

TE Part #6-1617540-4
J1MAP-6XL=M39016/7-016L

TE Part #624046-000
D-105-36



TE Part #279316-000
D-500-04-C23-072



TE Part #4-1617813-6
TD228-7500P=TDFO .75 SEC M83726 /28-7500P

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1617076-6_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-1617076-6_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1617076-6_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

5-1773450-5_sec1_3SBH

English