




PIDG

TE Internal #: 154708
PIDG, Crimp Wire Pins, Tabs & Ferrules, Tab, Blade, Crimp Wire
Pin, Tab & Ferrule Tab Width .12 in [3.05 mm], Tab Thickness .79
mm [.031 in]

[View on TE.com >](#)

Terminals & Splices > Crimp Wire Pins, Tabs & Ferrules



Terminal & Splice Type: **Tab**
Crimp Wire Pin, Tab & Ferrule Terminal Type: **Blade**
Crimp Wire Pin, Tab & Ferrule Tab Width: **3.05 mm [.12 in]**
Tab Thickness: **.79 mm [.031 in]**
Crimp Wire Pin, Tab & Ferrule Wire Insulation Diameter (Max): **3.36 mm [.132 in]**

Features

Product Type Features

Crimp Wire Pin, Tab & Ferrule Barrel Type	Closed Barrel
Crimp Wire Pin, Tab & Ferrule Wire/Cable Type	Regular Wire
Sealable	No
Insulated	Yes
Support Style	Insulation Support

Body Features

Sleeve Material	Nylon
Double Wire	No
Insulation Color	Red
Insulation Material	Nylon
Crimp Wire Pin, Tab & Ferrule Plating Material	Copper, Tin

Contact Features

Terminal Length	16.76 mm[.66 in]
Terminal & Splice Type	Tab
Crimp Wire Pin, Tab & Ferrule Terminal Type	Blade
Tab Thickness	.79 mm[.031 in]
Crimp Wire Pin, Tab & Ferrule Terminal Orientation	Straight

Termination Features

--	--



Bullet Terminal	Without
-----------------	---------

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Crimp Wire Pin, Tab & Ferrule Tab Width	3.05 mm[.12 in]
Crimp Wire Pin, Tab & Ferrule Wire Insulation Diameter (Max)	3.36 mm[.132 in]
Accepts Wire Insulation Diameter Range	2.67 – 3.36 mm[.105 – .14 in]
Wire Size	509 – 3260 CMA
	.145 in
Crimp Wire Pin, Tab & Ferrule Material Thickness	.79 mm[.032 in]
Crimp Wire Pin, Tab & Ferrule Overall Length	27.81 mm[1.09 in]

Usage Conditions

Insulation Requirement	Partially Insulated
Operating Temperature Range	105 °C[221 °F]

Operation/Application

Heavy Duty	No
------------	----

Packaging Features

Packaging Quantity	1000
Crimp Wire Pin, Tab & Ferrule Packaging Method	Box

Other

Barrel Color	Red
--------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content



Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 150300 22-16 PIDG NYLON R/T 5/16 RED	TE Part # 151793 22-16 LIPPED BLADE EXP.1	TE Part # 151733 22-16 R/T 2BA BLACK NYLONEX 14	TE Part # 151754 22-16 PIDG R/T BLACK NYLOEXP.1

Also in the Series | PIDG

Compression Connectors(17)	Crimp Terminal Housings(1)	Crimp Wire Pins, Tabs & Ferrules(41)	Knife Disconnects(11)
PCB Terminals(9)	Portable Crimp Tools(2)	Quick Disconnects(53)	Ring Terminals & Spade Terminals(862)



Special Purpose Terminals(1)



Splices(48)

Customers Also Bought



TE Part #165142
PIDG FORMED WIRE PINS



TE Part #151469
16-14 PIDG LIP'D BLADE BLACK E



TE Part #150730
22-16 PIDG TAB 3,3/3



TE Part #131331
PIDG TABS




TE Part #342062
16-14 H.D.R/T 5MM STUD BLACK




TE Part #342063
16-14 H.D.R/T 1/4" STUD BLACK



TE Part #151467
22-16 PIDG LIPPED BLADE EXP.1



TE Part #154724
16-14 PIDG BLADE EXP .165VINYL



TE Part #2825383002
44A0211-16-2



TE Part #EC6835-000
06151929-LC

Documents

Product Drawings

22-16 PIDG LIPPED BLADE EXP.1

English

Datasheets & Catalog Pages

RADIATION_RESISTANT_PRE-INSULATED_TERMINALS_SPLICES

English

Product Specifications



Application Specification

English