



Relays, Contactors & Switches > Relays > Mil-Aero Relays > Full-Size Relays



Full-Size Relay Contact Arrangement: **2 Form C, DPDT, 2 C/O**

Contact Base Material: **Silver Cadmium Oxide**

Full-Size Relay Input Voltage: **12 VDC**

Full-Size Relay Contact Current Rating: **10 A**

Coil Voltage: **12 VDC**

Features

Product Type Features

Enclosure Type	Hermetically Sealed
Coil Latching	Without
Product Type	Relay
Relay Type	Military/Aerospace High Performance
MOSFET Driver	Without

Configuration Features

Transistor Driver	Without
-------------------	---------

Electrical Characteristics

Actuating System	DC
Vibration	20G's, 10 – 2000Hz
Coil Magnetic System	Non-Polarized, Monostable
Shock	100G's, 6ms
Coil Suppression Diode	Without
Coil Polarity Protection Diode	Without
Full-Size Relay Input Voltage	12 VDC
Coil Voltage	12 VDC
Full-Size Relay Coil Resistance	75 Ω



Full-Size Relay Coil Power Rating (DC)	1920 mW
Coil Power Measurement	Milliwatts
Full-Size Relay Contact Switching Voltage (Max)	28 VDC

Contact Features

Full-Size Relay Contact Arrangement	2 Form C, DPDT, 2 C/O
Contact Base Material	Silver Cadmium Oxide
Full-Size Relay Contact Current Rating	10 A

Termination Features

Termination Type	Socket Pins
------------------	-------------

Mechanical Attachment

Full-Size Relay Mounting Type	Plain Case
-------------------------------	------------

Usage Conditions

Operating Temperature Range	-65 – 125 °C
-----------------------------	--------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for



substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts




TE Part # 1617754
FCA-410-1517M=M83536/15-017M

Customers Also Bought



TE Part #1-6609032-5
CORCOM R SERIES SINGLE PHASE
FILTERS



TE Part #1-1625971-3
Power Resistors: Aluminum Housed,
HSA



TE Part #1-1617004-0
B07D034BC2-0053 = M5757/23-005




TE Part #1-1761686-3
IDC LOW PRO HDR 40P VERT LG LAT



TE Part #1-1617076-9
3SBH1165A2 = M39016/14-008M




TE Part #HD18-009
DEUTSCH HD10 BACKSHELLS




TE Part #1-643067-8
18P MTA156 MOLDED COVER



TE Part #1-146261-5
30 MODII HDR DRST B/A .100CL



TE Part #1-1546310-0
10P.563" DR BARRIER STRIP



TE Part #1-116975-5
HSG-RECP ECONOMATE 2

Documents

CAD Files



3D PDF

3D

Customer View Model

ENG_CVM_CVM_1617004-9_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1617004-9_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1617004-9_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

5-1773450-5_sec1_07

English

RELAY

English