



CII

TE Internal #: 1617128-8

TO-5/.100 Grid Relays, 2 Form C, DPDT, 2 C/O, 18VDC TO-5/.100

Grid Relay Input Voltage, Coil Suppression Diode

[View on TE.com >](#)

Relays, Contactors & Switches > Relays > Mil-Aero Relays > TO-5/.100 Grid Relays



TO-5/.100 Grid Relay Contact Arrangement: 2 Form C, DPDT, 2 C/O

TO-5/.100 Grid Relay Input Voltage: 18 VDC

Coil Suppression Diode: With

MOSFET Driver: Without

Transistor Driver: Without

Features

Product Type Features

Enclosure Type	Hermetically Sealed
Relay Type	Military/Aerospace High Performance
Coil Latching	Without
Product Type	Relay
MOSFET Driver	Without

Configuration Features

Transistor Driver	Without
-------------------	---------

Electrical Characteristics

Coil Magnetic System	Non-Polarized, Monostable
Vibration	30G's, 10 – 3000Hz
Actuating System	DC
Shock	75G's, 6ms
Coil Power Measurement	Milliwatts
TO-5/.100 Grid Relay Input Voltage	18 VDC
Coil Suppression Diode	With
Coil Voltage	18 VDC
TO-5/.100 Grid Relay Coil Resistance	1600 Ω
TO-5/.100 Grid Relay Coil Power Rating (DC)	203 mW



Coil Polarity Protection Diode	With
TO-5/.100 Grid Relay Contact Switching Voltage (Max)	28

Contact Features

Contact Current Class	Low Level – 1 A
TO-5/.100 Grid Relay Contact Arrangement	2 Form C, DPDT, 2 C/O
TO-5/.100 Grid Relay Contact Current Rating	1 A

Termination Features

Termination Type	PC Pins
------------------	---------

Mechanical Attachment

TO-5/.100 Grid Relay Mounting Type	Printed Circuit Board
------------------------------------	-----------------------

Usage Conditions

Operating Temperature Range	-65 – 125 °C
-----------------------------	--------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUL 2019 (201) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not lead free process capable

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides



on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1617036-6
HFW4A1201D00 = HFW 4A RELAY

Customers Also Bought

TE Part #1-1617110-2
JMGST-18M = M28776/7-005M

TE Part #1-88637-0
2.54mm FFC Connectors Receptacle Housing

TE Part #212933-2
PLUG ASSY,104 POSN,AMPLIMITE

TE Part #1883500-2
BLINDMATE PLUG SZ 4

TE Part #446853-5
3ROW BOX REC 165P 100CLSEALED

TE Part #448821-1
KIT,TWINAX BOARD MOUNT 4 POS

TE Part #66750-2
CONT,CR,ACTIVE FOR 22 AWG WIRE

TE Part #1616056-7
A400F=CONTACTOR-CONTINUOUS DUT

TE Part #1-1617353-1
JMACT-26XL=M28776/1-030L

TE Part #4-1617559-0
SR-7622=M39016/40-022

Documents

- CAD Files
- 3D PDF
- 3D



Customer View Model

[ENG_CVM_CVM_1617128-8_O.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1617128-8_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1617128-8_O.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[5-1773450-5_sec1_MS](#)

English