




Cable Assemblies > Copper Cable Assemblies > Pluggable I/O Cable Assemblies



Pluggable I/O Cable Assembly Type: **MOW to PB**

Keyed Position: **1**

Equalized: **No**

Wire Size: **159.8 – 159.88 mm²**

Features

Product Type Features

Product Type	Cable Assembly
Product Designation	Patch Cord
Cable Assembly Category	Industry Standard
Pluggable I/O Cable Assembly Type	MOW to PB
Pluggable I/O Cable Assembly Shielded	No
Pluggable I/O Cable Assembly Connector Type (End A)	Male-On-Wire
Pluggable I/O Cable Assembly Connector Type (End B)	Paddleboard
Pluggable I/O Cable Assembly Cable Style	Ribbon Cable

Configuration Features

Configuration	Double-Ended
Keyed Position	1
Number of Pluggable I/O Cable Assembly Positions	6
Number of Signal Positions	6
Pluggable I/O Cable Assembly Keyed	Yes

Body Features

Equalized	No
Pluggable I/O Cable Assembly Color	Gray

Dimensions

--	--



Wire Size	159.8 – 159.88 mm ²
-----------	--------------------------------

Operation/Application

Halogen Free	No
--------------	----

Industry Standards

IEEE 1394	No
Pluggable I/O Cable Assembly Flammability Rating	UL 2651

Other

CLOUDSPLITTER	No
Cable Assembly Length	.15 m[.492 ft]

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-M5833-F3492A
FEMALE-ON-BOARD CONNECTOR
TOP ENTRY

Also in the Series | Micro-MaTch Industrial

Board-to-Board Headers & Receptacles(1)

Insertion & Extraction Tools(1)

Pluggable I/O Cable Assemblies(52)

Ribbon Cable Connectors(204)

Wire-to-Board Connector Contacts(4)

Customers Also Bought

TE Part #9-160463-2
PIDG PIGGY BACK FASTON
TERMINAL

TE Part #1623799-3
Wirewound Resistor: Vertical Mount

TE Part #1734035-2
MINI USB, TYPE B, R/A, SMT

TE Part #1676271-2
RN 0805 26K1 0.1% 10PPM 1KRL

TE Part #1-2213753-3
4 POS HIGH TEMP MATE-N-LOK
SOCKET ASSM

TE Part #1-2213753-4
5 POS HIGH TEMP MATE-N-LOK SKT
ASSM

TE Part #1473005-4
DDR2 SO DIMM Sockets

TE Part #1-1969598-8
18P FH PLUG VAL-U-LOK V2



Documents

Product Drawings

CA MICRO-MATCH MOW-PB 6POS

English

Product Specifications

Application Specification

English

micro match miniature connector system

English