



## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (.6% in Component part) <b>Article Safe Usage Statements:</b> Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Customers Also Bought



TE Part #1-281838-0  
HE13/HE14 Crimp Housings



TE Part #1825011-1  
ASF2204=DPDT AUTOSLIDE



TE Part #1393776-4  
V23026D1022B201 \*X020



TE Part #1-1825007-1  
DRD16CE04=ROT DIP,16P



TE Part #1-2176092-9  
RP 2A 0.25W 1K02 0.1% 25PPM 1K RL



TE Part #1676152-2  
RN 0805 10K7 0.1% 10PPM 1KRL



TE Part #1-2176389-5  
RQ 1206 150R 0.1% 10PPM 5K RL



TE Part #9-1879129-2  
RN 0402 2K49 0.1% 10PPM 1K RL



TE Part #2-1571586-9  
DIP Socket: Standard, Screw Machine,  
Open, Gold

## Documents

### Product Drawings

824-AG31D-LF=800 DIP,PCB,AU/SN

English

### CAD Files

Customer View Model

[ENG\\_CVM\\_3-1571586-6\\_B.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_3-1571586-6\\_B.3d\\_stp.zip](#)

English

Customer View Model

[ENG\\_CVM\\_3-1571586-6\\_B.2d\\_dxf.zip](#)

English

### 3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.