



Agastat 7000

TE Internal #: 9-1768047-6

Agastat 7000, Pre-Printed Markers, Snap-On, STD 24 Marker Size,
Compatible Cable Diameter Range 15 – 19 mm [.59 – .75 in],
Straight Cut

[View on TE.com >](#)

Identification & Labeling > Pre-Printed Markers > STD SNAP-ON MARKERS



Marker Style: **Snap-On**

Marker Size: **STD 24**

Compatible Cable Diameter Range: **15 – 19 mm [.59 – .75 in]**

Marker Cut: **Straight**

Printed Marking: -

[All STD SNAP-ON MARKERS \(881\)](#)

Features

Body Features

Marker Style	Snap-On
Marker Size	STD 24

Dimensions

Compatible Cable Diameter Range	15 – 19 mm [.59 – .75 in]
---------------------------------	---------------------------

Printer/Label Features

Marker Cut	Straight
Printed Marking	-

Packaging Features


Packaging Method	Box
Packaging Quantity	50

Other

Printed Marking Color	Black
-----------------------	-------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)





EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | Agastat 7000



Pre-Printed Markers(888)




Time Delay Relays(214)

Customers Also Bought



TE Part #3-1393480-7
D-Sub Receptacle Assy: Eurostyle, Right Angle, 2.74mm



TE Part #7-1377174-7
SMP 0-0165619-2



TE Part #2-167495-4
48P.IEC-F MALE CONN




TE Part #2-106506-2
D-Sub Receptacle Assembly: Right Angle, Shell Size 2, 2.74mm



TE Part #1825290-6
MHS233GRA04=DP3T SL SW R/A AU



TE Part #2-215299-1
21P HV100 REC CON. TE, 8.5MM



TE Part #3-100318-2
DUAL LOADED



TE Part #5338048-6
6P. DIP SWITCH WITH ACTION PIN POSTS



TE Part #5338048-8
8P. DIP SWITCH WITH ACTION PIN POSTS



TE Part #966260-1

Documents

Product Drawings
STD24W-MINUS

English

Datasheets & Catalog Pages
STD and STB Technical Datasheet

English

IDENTIFICATION SELECTION GUIDE

English



Product Specifications

RW-2538 STD and STB work instruction

English