

TE Internal #: 4-1768017-7

Standard Labels, Blank Labels, Die-Cut Label Style, Permanent, UL Listed No, Label Width 15 mm [.591 in], Label Height .25 in [6.35 mm], Silver

[View on TE.com >](#)



Identification & Labeling > Labels > Standard Labels



Label Type: **Blank Labels**

Label Style: **Die-Cut**

Label Adhesive Type: **Permanent**

UL Listed: **No**

Label Width: **15 mm [.591 in]**

Features

Product Type Features

Label Type	Blank Labels
------------	--------------

Body Features

Label Color	Silver
-------------	--------

Usage Conditions

Operating Temperature Range	0 – 70 °C[32 – 158 °F]
-----------------------------	------------------------

Printer/Label Features

Recommended Printer	See TE Document 411-121005 the Printer Product Ribbon Matrix
Recommended Printer Ribbon	See Printer Ribbon Matrix
Printer Technology	Thermal Transfer
Label Style	Die-Cut
Label Width	15 mm[.591 in]
Label Height	6.35 mm[.25 in]
Label Material	Polyester

Industry Standards

UL Listed	No
-----------	----

Packaging Features

Packaging Quantity	10000
--------------------	-------



Other

Label Adhesive Type	Permanent
---------------------	-----------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 9-1768017-3
[EET-0820P-8A](#)



TE Part # 4-1768017-1
[EET-0606P-8A](#)

Customers Also Bought





TE Part #1625826-8

Metal Chip Resistor: Current Sense



TE Part #102153-2

AMP-LATCH UNIVERSAL HEADERS




TE Part #1648115-1

222-0010-01100=SA CONN,SKT



TE Part #1419108-1

RT114012



TE Part #1393738-3

V42254A6000G125=SUB D GEHAEUSE



TE Part #2-1393561-9

V42254A 262V 19=SUB D SCHRAUBE



TE Part #1-770166-0

02P MINI-UMNL ASSY VO SNNI*



TE Part #1-827064-0

10P MOD2 STIFT LEI



TE Part #1744055-4

3.96 EP HDR ASSY 4P VERT HT



TE Part #E21596-000

EP-101508-2.5-9

Documents

Product Drawings

EET-0615P-8A

English

Datasheets & Catalog Pages

TTDS-175, EET...P-8A

English