




Relays, Contactors & Switches > Relays > Mil-Aero Relays > Mid-Range Relays



Mid-Range Relay Contact Arrangement: 1 Form C, SPDT, 1 C/O

Coil Suppression Diode: Without

Auxiliary Contacts: Without

Terminal Plating: Tin-Lead

Mid-Range Relay Contact Current Rating: 25 A

Features

Product Type Features

Enclosure Type	Hermetically Sealed
Terminal Configuration	Solder Pins
Product Type	Relay
Relay Type	Military/Aerospace Mid-Range

Electrical Characteristics

Vibration	30G's, 10 – 3000Hz
Shock	200G's, 6ms
Coil Suppression Diode	Without
Mid-Range Relay Coil Voltage Rating	28 VDC
Mid-Range Relay Coil Resistance	320 Ω
Back EMF Suppression	Without
Coil Magnetic System	Polarized, Monostable
Actuating System	DC

Signal Characteristics

Frequency	400 Hz
-----------	--------

Contact Features

Mid-Range Relay Contact Arrangement	1 Form C, SPDT, 1 C/O
Auxiliary Contacts	Without
Terminal Plating	Tin-Lead



Mid-Range Relay Contact Current Rating	25 A
Contact Base Material	Silver Cadmium Oxide

Mechanical Attachment

Mid-Range Relay Mounting Type	Raised Vertical Flange Mount
-------------------------------	------------------------------

Usage Conditions

Operating Temperature Range	-70 – 125 °C
-----------------------------	--------------

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not lead free process capable

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 5-1617753-0
FCA-325-BZ4



TE Part # 3-1617753-7
FCA-325-AY2




TE Part # 5-1617814-4
FCA-325-BZ9



TE Part # 9-1617805-3
FCA-150-KX4=50 AMP 1PST/NO DM RELAY




TE Part # 4-1617813-3
FCA-325-AZ3



TE Part # 6-1617753-4
FCA-325-CY3



TE Part # 2-1617801-4
FCAC-150-KR3=50 AMP W/AUX RELAY



TE Part # 6-1617806-8
FCAC-325-AV8=RELAY, 3PST W/AUX



TE Part # 3-1617814-9
FCAC-150-KX3=50 AMP MID-RANGE RELAY




TE Part # 4-1617753-0
FCA-325-AY5




TE Part # 1-1617795-0
FCA-150-BY4=Relay



TE Part # 7-1617794-9
FCA-150-CU2=Relay



TE Part # 4-1617753-5
FCA-325-BY2



TE Part # 5-1617753-4
FCA-325-CW2




TE Part # 1617780-3
FCA-325-CZ4




TE Part # 1-1617815-1
FCAC-150-CY4=50 AMP MID RANGE AUX RELAY



TE Part # 9-1617815-6
FCAC-325-AV6=RELAY, 3PST W/AUX



TE Part # 7-1617806-3
FCAC-325-BX3=RELAY, 3PST W/AUX



TE Part # 8-1617806-8
FCAC-325-CX4=RELAY, 3PST W/AUX

Also in the Series | CII FCA-125 Series



Mid-Range Relays(84)


Customers Also Bought



TE Part #4-2176371-6
RQ 0603 13K7 0.1% 10PPM 5K RL



TE Part #1617754-3
FCA-410-1522M=M83536/15-022M




TE Part #1053254-1
2058 5278 00 SMA FEEDTHRU JACK,
SEALED



TE Part #443975-4
AMPLIMITE, RCPT ASY, POSTD, 109,4



TE Part #204517-3
AMPLIMITE, ASY, PLUG, STD, 90,3, KIT



TE Part #189651-000
22759/43-16-5



TE Part #YDIV46E17-06SNC128
PLUG ASSY



TE Part #1616007-1
BA104WA1=RELAY



TE Part #1617029-8
HFW1130G02 = M39016/6-211L



TE Part #1617352-5
JMSC-26XLS=M39016/11-044L

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_4-1617748-6_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_4-1617748-6_B.3d_igs.zip



English

Customer View Model

[ENG_CVM_CVM_4-1617748-6_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[5-1773450-5_sec5_FCA-125](#)

English

RELAY

English