



Product Compliance

For compliance documentation, visit the product page on TE.com>

|   |   |
|---|---|
| EU RoHS Directive 2011/65/EU                  | Out of Scope  |
| EU ELV Directive 2000/53/EC                   | Out of Scope  |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Not reviewed for China RoHS compliance  |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2021 (211)<br>Candidate List Declared Against: JAN 2019 (197)<br>SVHC > Threshold:<br>Not Yet Reviewed |
| Halogen Content                               | Not Yet Reviewed for halogen content  |
| Solder Process Capability                     | Not applicable for solder process capability  |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # 414048-6  
CABLE PLUG,FEMALE,RTANG SMB



TE Part # 414618-2  
SMB PLUG 75 OHM



TE Part # CAT-884-SMBM50  
SMB Connector: Male (Jack), Mated Outer Dia. 4.75mm, 50 Ohm



TE Part # 414618-1  
75 OHM SMB PLUG



TE Part # 414948-1  
CONNECTOR,JACK,SER SMB

Customers Also Bought



TE Part #413985-1  
SMB Connector: Female (Plug), Mated Outer Dia. 4.75mm, 50 Ohm



TE Part #1-1827872-5  
DYNAMIC 1100 HDR ASSY



TE Part #1735446-3  
AMP HPI 2.0MM HEADERS



TE Part #1735447-3  
AMP HPI 2.0MM RECEPTACLE HOUSINGS



TE Part #354940-1  
PRO-CRIMPER III FRAME W/O DIES



TE Part #36189  
BUDG R 22-16 COMM 22-18 MIL 4



TE Part #1-1393779-3  
V23101D 6A201



TE Part #4-794630-8  
18P MICRO MNL ASSY,VRT,HDR,LF



TE Part #227426-1  
BNC BLKHD RECPT SEALED

Documents



Datasheets & Catalog Pages

1-1773865-2\_1015\_Commercial Manual Hand Tools

English

Instruction Sheets

Instruction Sheet (U.S.)

English

AMP HEX CRIMPING DIE ASSEMBLY 58489-1

English