



Identification & Labeling > Pre-Printed Markers > STD SNAP-ON MARKERS



Marker Style: **Snap-On**
Marker Size: **STD 21**
Compatible Cable Diameter Range: **11 – 15.5 mm [.433 – .61 in]**
Marker Cut: **Straight**
Printed Marking: **N**

[All STD SNAP-ON MARKERS \(881\)](#)

Features

Body Features

Marker Style	Snap-On
Marker Size	STD 21

Dimensions

Compatible Cable Diameter Range	11 – 15.5 mm [.433 – .61 in]
---------------------------------	------------------------------

Printer/Label Features

Marker Cut	Straight
Printed Marking	N

Packaging Features


Packaging Method	Box
Packaging Quantity	50

Other

Printed Marking Color	Black
-----------------------	-------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)





EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | Agastat 7000




Pre-Printed Markers(888)



Time Delay Relays(214)

Customers Also Bought



TE Part #2-1586041-0
20P VAL-U-LOK R/A HDR V2



TE Part #8-215460-6
MICRO-MATCH FSID P



TE Part #1-1393774-7
V23026A1006B201



TE Part #EJ1954-000
Z-TYPE PUSH-ON MARKERS



TE Part #1-1623931-9
CFR25 5% 39R




TE Part #2-1623931-9
CFR25 5% 3R9




TE Part #8-1623931-4
CFR25 5% 8R2



TE Part #2-1393774-0
V23026C1051B201



TE Part #2-2176373-6
RQ 0805 18R2 0.1% 10PPM 1K RL



TE Part #4-2176373-1
RQ 0805 26R1 0.1% 10PPM 1K RL

Documents

Product Drawings

STD21Y-N

English

Datasheets & Catalog Pages

STD and STB Technical Datasheet

English

IDENTIFICATION SELECTION GUIDE

English



Product Specifications

RW-2538 STD and STB work instruction

English