234A111-25/86-0 ✔ ACTIVE

Raychem

TE Internal #: 749665-000

D-Sub Connector Boots, 90° Boot Angle, Adhesive Pre-Coating, High Performance Pre-Coat Adhesive, 0 Position, 0mm [0in] Centerline

View on TE.com >

Connectors > D-Shaped Connectors > D-Sub Accessories > D-Sub Connector Boots



Boot Angle: **90°**

Adhesive Pre-Coating: **With**

Adhesive Description: **High Performance Pre-Coat Adhesive**

Number of Positions: **0**

Centerline (Pitch): **0 mm [0 in]**

Features

Product Type Features

Product Type	Molded Boot
Molded Part Type	D Subminiature Boot
Adhesive Description	High Performance Pre-Coat Adhesive

Configuration Features

Number of Positions	0

Body Features

Material Systems Code	25
Material	Fluid Resistant Modified Elastomer
Material Code	25
Boot Angle	90°
Adhesive Pre-Coating	With

Contact Features

Contact Current Rating (Max)	0 A

Housing Features

Centerline (Pitch)	0 mm[0 in]

Dimensions

Connector Width	10.7 mm[.421 in]

Usage Conditions

Operating Temperature Range	-75 – 150 °C[-103 – 302 °F]

Other

Adhesive Code	86
Adhesive Options	/86 Precoat

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # CJ2087-000
HL2010E-KIT-120V

Customers Also Bought

TE Part #475683-000
D-SCE FLUID RESISTANT SLEEVES


TE Part #YDTS20Z13-35PBV001
D38999: Square Flange, 13-35 insert

TE Part #5054574004
Single Wall RNF-100 Flat Spool HST

TE Part #2-1879450-7
Wirewound Resistor: Mineral, 2.5 Kw



TE Part #201359-3
MALE BLOCK 26 PL.



TE Part #284040-002
44A0211-4-9




TE Part #3782863001
44A1122-20-2/6-9



TE Part #6594333001
55A0111-22-45



TE Part #6418013001
55A1124-24-0/9-9



TE Part #511319-000
TXR61AB00-1407AI

Documents

Product Drawings

234A111-25/86-0

English

Datasheets & Catalog Pages

1654025_Sec4_-25

English

Raychem Molded Parts Visual Guide

English

Product Specifications

Product Specification

English

Product Environmental Compliance

Safety Datasheet

Safety Datasheet

German

Safety Datasheet

German

Safety Datasheet

English

Safety Datasheet

English

Safety Datasheet

Safety Datasheet

Safety Datasheet

French

Safety Datasheet

French

Safety Datasheet

Safety Datasheet

Safety Datasheet

Safety Datasheet

Safety Datasheet

Safety Datasheet