




Connectors > D-Shaped Connectors > D-Sub Accessories > D-Sub Connector Boots



Boot Angle: **Straight**
Adhesive Pre-Coating: **Without**
Adhesive Description: **Adhesive Purchased Separately**
Number of Positions: **0**
Centerline (Pitch): **0 mm [0 in]**

Features

Product Type Features

Product Type	Molded Boot
Molded Part Type	D Subminiature Boot
Adhesive Description	Adhesive Purchased Separately

Configuration Features

Number of Positions	0
---------------------	---

Body Features

Material Systems Code	10
Material	Polyolefin Flexible Modified
Material Code	4
Boot Angle	Straight
Adhesive Pre-Coating	Without

Contact Features

Contact Current Rating (Max)	0 A
------------------------------	-----

Housing Features

Centerline (Pitch)	0 mm[0 in]
--------------------	------------

Dimensions

Connector Width	10.7 mm[.421 in]
-----------------	------------------



Usage Conditions

Operating Temperature Range	-55 – 135 °C[-67 – 275 °F]
-----------------------------	----------------------------

Other

Adhesive Code	S1125
Comment	Contact Raychem for additional adhesive and/or cut off boot length information
Adhesive Options	S1006 Separate Adhesive, S1017 Separate Adhesive, S1030 Separate Adhesive, S1048 Separate Adhesive, S1125 Separate Adhesive

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # 890060-000
[S1017-1.0X50](#)



TE Part # CJ2087-000
[HL2010E-KIT-120V](#)

Customers Also Bought



TE Part #170204-2
[EIS CONTACT](#)



TE Part #171822-3
[EIS REC. HSG 3P-NATURAL](#)



TE Part #66332-3
[III+ PIN,24-20,15AU/FL,STRIP](#)



TE Part #5207719-1
[KIT SCREWLOCK FEMALE](#)



TE Part #4-641148-6
[16P MTA156 ASSY 18AWG ORA LF](#)




TE Part #187788-000
[SO63-3-00](#)



TE Part #2221860-4
[AMPLIMITE IP67,SZ4, 90, 62 POS,IFS, PLUG](#)



TE Part #3-1123723-1
[3.96 EP HDR ASSY 11P\(BLUE\) PLUG](#)



TE Part #6-103945-0
[2X11 MTE SHRD PIN SR LTCH .100](#)



TE Part #ZPF100000000007530
[983-0SE 12-03 SN-L](#)

Documents

Product Drawings

[214A042-4-0](#)

English

Datasheets & Catalog Pages

[1654025_Sec4_-4](#)

English

Raychem Molded Parts Visual Guide

English



Product Specifications

[Product Specification](#)

English

Product Environmental Compliance

[Safety Datasheet](#)

[Safety Datasheet](#)

German

[Safety Datasheet](#)

English

[Safety Datasheet](#)

[Safety Datasheet](#)

French

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)